





Notes:

- Electrical Specifications:
 - Meets USB 2.0 Specification
 - Contact Resistance: 30 mOhm max.
 - Insulation Resistance: 1000 MOhm min. @ 100 VDC
 - Current Rating: 1.5 A max. at 25° C
 - Working Voltage: 30 V (RMS) max.
 - DWV: 500 VAC/60s at sea level
 - Operating Temperature: -40° C to +85° C

2. Material and Finish:

- Receptacle Housing: Polyester (Black), UL94 V-0
- Cover Coupling Ring: Polyester (Black), UL94 V-0
- Panel Nut: Brass, Finish: Nickel Plated
- Panel Gasket: Silicone, Color: White
- Cover Gasket: Silicone, Color: Red
- USB Adaptor Metal Shell: Copper Alloy, Nickel Plated
- USB Adaptor Overmold material: PBT UL94 V-0, Color: Black
- USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel

3. Connector can be front or rear mounted to a maximum panel thickness of 3.2 mm.

4. RoHS compliant

Pin-Assingment

Type A F	Type A F
Pin1 -----	Pin1
Pin2 -----	Pin2
Pin3 -----	Pin3
Pin4 -----	Pin4
Shell -----	Shell

Directive 2002/95/EC
"RoHS"
Compliant

THIS DRAWING MAY NOT BE COPIED, REPRODUCED, OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°	Autodesk Inventor	Scale: 1:2:1	Dim. in mm
	Name	Title	Approval Date				
DOT NOT ALTER CAD DRAWING BY HAND				2008	Date	Name	Title: IP67 USB Receptacle + Cover Assembly Kit with USB 2.0 Type A F/ F Adaptor
				Draw.	Sept. 09	Vincent Ke	
				Appd.	Sept. 09	J. Chaudry	
				Norm			
				D-old			Drawing No.: 17K1A100
	a	original					Part No.: 17-200161
	Rev.	Changes	Date	Name			

CONEC

DIN
A3
Sheet
1/1