







LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	DWN
CM	00	AH3	REV PER ECR	12-000507	10JAN12	JR

- 1
- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
- 2
- SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [.5 LBS].
- 3
- DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
- 4
- FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 5
- UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE ON ANY SIDE OF HOUSING.
- 6
- POSITION #1 LOCATOR FEATURE MAY BE ROUND OR OBLONG (AS DEPICTED).
- 7
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 8
- SHOWN FOR CONVENIENCE; AMP LOGO MAY BE ON ANY EXTERNAL SURFACE.



3-DIMENSIONAL MODEL NTS



DETAIL A
OPTIONAL CONSTRUCTION

OBSOLETE	BLACK	1-480698-9
	GRAY	1-480698-8
OBSOLETE	BLUE	1-480698-6
	GREEN	1-480698-5
OBSOLETE	YELLOW	1-480698-4
	ORANGE	1-480698-3
OBSOLETE	RED	1-480698-2
	BROWN	1-480698-1
OBSOLETE	NATURAL	1-480698-0
	COLOR	PART NUMBER

27.43	1.080
14.73	.580
13.97	.550
11.68	.460
7.62	.300
0.38	.015
0.13	.005
MM	IN
CONVERSION TABLE	

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 22JUL05	TE Connectivity	
		CHK S. RIDGILL 22JUL05		
DIMENSIONS: mm		APVD S. RIDGILL 22JUL05	NAME	
		PRODUCT SPEC		
		APPLICATION SPEC		
		WEIGHT		
MATERIAL NYLON		FINISH -		
		CUSTOMER DRAWING		
		SCALE 4:1		
		SHEET 1 of 1		
		REV AH3		