



1:CRIMPED CONTACT  
HEX CRIMP SIZE: .137"  
2:CRIMPED FERRULE  
HEX CRIMP SIZE: .429"



Impedance	50Ω
Ferquency range	0-6 GHz
Voltage rating	1500 volts peak
Dielectric withstanding voltage	2500 volts rms
VSWR	M39012 straight connectors:1.3max,0-11GHz M39012 right angle:1.35 max,0-11GHz
othr (MIL-C-39012 cable connectors)	Contact resistance: center contact 1.0 milliohm outer contact 0.2 milliohm Insertion loss:0.15db max at 10.0GHz Insulation resistance:5000 megohms(mln)

NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER JIS-C3604
2. TEFLON MIL-P-19468
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL 70 u" THICK OVER COPPER STRIKE
6. GOLD PL 1-3u" OVER NICKEL PL 70 u" THICK OVER COPPER STRIKE

7	Washer	Brass	Nickel
6	Nut	Brass	Nickel
5	Ferrule	Brass	Nickel
4	Shell	Brass	Nickel
3	Insulator	Teflon(PTFE)	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish

744747