

**tension spring terminal roof style
ZDU 2.5-2/3AN BL**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Terminal blocks in tension clamp system and the Z Series are specially customised to the customers' requirements. Less space, spacious labelling area, integrated test point, cross-connection functionality within the Z Series and another family of terminals by Weidmüller. Z-Series terminals have a large clamping range and one or two cross-connection slots. Plug-in standard cross-connections enable potentials to be distributed over any number of terminals.

General ordering data

| | |
|------------|---|
| Type | ZDU 2.5-2/3AN BL |
| Order No. | 1706040000 |
| Version | tension spring terminal roof style, Feed-through terminal, Rated cross-section: Tension clamp connection, Wemid, Blue |
| GTIN (EAN) | 4008190915391 |
| Qty. | 100 pc(s). |

tension spring terminal roof style ZDU 2.5-2/3AN BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|--------------------------|--------|
| Length | 50.5 mm | Width | 5.1 mm |
| Height | 43 mm | Height of lowest version | 44 mm |
| Net weight | 6.66 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature | | Storage temperature | |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Rated data IECEx/ATEX

| | | | |
|---------------------------------|---|--------------------------------|--------------------------|
| Certificate No. (ATEX) | KEMA97ATEX4677U | ATEX certificate | KEMA97ATEX4677U_d.pdf |
| ATEX certificate | KEMA97ATEX4677U_e.pdf | Certificate No. (IECEX) | IECEXULD05.0009U |
| IEC Ex certificate | IECEXULD05.0009U_e.pdf | Max. voltage (ATEX) | 550 V |
| Current (ATEX) | 21 A | Wire cross section max. (ATEX) | 2.5 mm ² |
| Max. voltage (IECEX) | 550 V | Current (IECEX) | 20 A |
| Wire cross section max. (IECEX) | 2.5 mm ² | Voltage, cross-connection | CrossConnectionGuide.pdf |
| Operating temperature range | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7 | |
| Marking ATEX Directive 94/9/EC | II 2 G D | | Ex e II |

Additional technical data

| | | | |
|--------------------------|--|-----------------------------|---------|
| Explosion-tested version | Yes | Number of similar terminals | 1 |
| Open sides | right | Type of mounting | Snap-on |
| Version | Tension-clamp connection, for plug-in cross-connector, One end without connector | | |

CSA ratings data

| | | | |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA) | 200039-1194786 | Voltage size C (CSA) | 600 V |
| Current size C (CSA) | 23 A | Wire cross section max. (CSA) | 14 AWG |
| Wire cross section min. (CSA) | 26 AWG | | |

Clampable wires (additional connection)

| | | | |
|---|---------------------|---|---------------------|
| Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min. | 0.5 mm ² | Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max. | 2.5 mm ² |
|---|---------------------|---|---------------------|

tension spring terminal roof style ZDU 2.5-2/3AN BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Clampable wires (rated connection)

| | | | |
|---|--------------------------|---|----------------------|
| Type of connection | Tension clamp connection | Stripping length | 10 mm |
| Blade size | 0.6 x 3.5 mm | Connection direction | Inclined / angled |
| Number of connections | 3 | Clamping range, rated connection, min. | 0.13 mm ² |
| Clamping range, rated connection, max. | 4 mm ² | Gauge to IEC 60947-1 | A2 |
| Wire connection cross section, solid core, max. rated connection | 0.5 mm ² | Wire connection cross section, solid core max. rated connection | 4 mm ² |
| Wire connection cross section, finely stranded, max. | 2.5 mm ² | Wire connection cross-section, finely stranded, min. | 0.5 mm ² |
| Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min. | 0.5 mm ² | Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max. | 2.5 mm ² |
| Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max. | 1.5 mm ² |
| Wire connection cross section AWG, min. | AWG 26 | Wire connection cross section AWG, max. | AWG 12 |

Rated data

| | | | |
|---------------|---------------|---------------------------------|------|
| Rated voltage | 800 V | Rated impulse withstand voltage | 8 kV |
| Rated current | 24 A | Current at maximum wires | 24 A |
| Standards | IEC 60947-7-1 | Pollution severity | 3 |

UL ratings data

| | | | |
|---|--------|---|--------|
| Certificate No. (UR) | E60693 | Voltage size C (UR) | 600 V |
| Current size C (UR) | 20 A | Conductor size Factory wiring max. (UR) | 12 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Field wiring max. (UR) | 12 AWG |

Material data

| | | | |
|---------------------|-------|---------------------------|-------|
| Insulating material | Wemid | Material | Wemid |
| Colour | Blue | UL 94 flammability rating | V-0 |

System specifications

| | | | |
|-----------------------------------|------------------------------------|----------------------------------|--------------------------|
| Product family | tension spring terminal roof style | Type of connection | Tension clamp connection |
| Connection direction | Inclined / angled | Number of levels | 1 |
| Number of connections | 3 | No. of clamping points per level | 3 |
| Levels cross-connected internally | No | Mounting rail | TS 35 |
| End cover plate required | Yes | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000897 | UNSPSC | 30-21-18-11 |
| eClass 5.1 | 27-14-11-20 | eClass 6.2 | 27-14-11-20 |
| eClass 7.1 | 27-14-11-20 | | |

Product information

| | |
|---------------------------------|---|
| Descriptive text ordering data | Rated voltage is reduced to 400 V when using the cross-connector. |
| Descriptive text technical data | 2.5 mm ² flexible wires with wire-end ferrules are crimped with the Weidmüller PZ 6/5 crimping tool. |
| Descriptive text accessories | The rated voltage is decreased to 250 V when using the shielding rail LS 2.8 (1056400000). |

Datenblatt

**tension spring terminal roof style
ZDU 2.5-2/3AN BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS

Conform