

P-series PDL 4/L/L/PE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



We have added the new three-wire installation terminal series with the PUSH IN direct-insert connection system to our already extensive range of modular terminals. They are especially suitable for power distribution in building installations, and wiring is made very convenient with the Roof Style terminals. The technical data clearly demonstrate this:

Featuring the performance specifications of a 4 mm² terminal with the smaller size typical of a 2.5 mm² terminal.

General ordering data

Type	PDL 4/L/L/PE
Order No.	1882610000
Version	P-series, Installation multi-tier terminal, Rated cross-section: 4 mm ² , PUSH IN
GTIN (EAN)	4032248485918
Qty.	50 pc(s).

P-series PDL 4/L/L/PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	100 mm	Width	5.1 mm
Height	48.5 mm	Height of lowest version	49.5 mm
Net weight	22.96 g		

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Explosion-tested version	No	Open sides	right
Type of mounting		Version	PUSH IN connection, L, L and PE connection, for plug-in cross-connector, One end without connector
	Snap-on		

CSA ratings data

Certificate No. (CSA)	200039-1751332	Voltage size B (CSA)	300 V
Current size B (CSA)	20 A	Wire cross section max. (CSA)	10 AWG
Wire cross section min. (CSA)	28 AWG		

Clampable wires (rated connection)

Type of connection	PUSH IN	Stripping length	12 mm
Blade size	3.0 x 0.5 mm	Connection direction	top
Clamping range, rated connection, min.	0.08 mm ²	Clamping range, rated connection, max.	4 mm ²
Gauge to IEC 60947-1	A3	Wire connection cross section, solid core, max. rated connection	0.5 mm ²
Wire connection cross section, solid core max. rated connection	4 mm ²	Wire connection cross section, stranded, rated connection, min.	1.5 mm ²
Wire connection cross section, stranded, rated connection, max.	4 mm ²	Wire connection cross section, finely stranded, max.	4 mm ²
Wire connection cross-section, finely stranded, min.	0.5 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	4 mm ²	Cross-section for connected conductor, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules and plastic collars DIN 46228/4, rated connection, max.	2.5 mm ²	Twin wire-end ferrules, min.	0.5 mm ²
Twin wire-end ferrules, max.	1.5 mm ²		

Rated data

Rated cross-section	4 mm ²	Rated voltage	400 V
Rated impulse withstand voltage	6 kV	Rated impulse withstand voltage to adjacent terminal	6 kV
Rated current	32 A	Pollution severity	3

Datenblatt

**P-series
PDL 4/L/L/PE**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

UL ratings data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	10 AWG
Conductor size Factory wiring min. (cURus)	28 AWG	Conductor size Field wiring max. (cURus)	10 AWG
Conductor size Field wiring min. (cURus)	28 AWG	Current size B (cURus)	17 A
Current size D (cURus)	10 A	Voltage size B (cURus)	300 V
Voltage size D (cURus)	300 V		

Material data

Material	Wemid	Colour	Yellow, Green
UL 94 flammability rating	V-0		

System specifications

Product family	P-series	Type of connection	PUSH IN
Connection direction	top	Number of levels	2
Levels cross-connected internally	No	Mounting rail	TS 35

Classifications

ETIM 3.0	EC001329	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-25	eClass 6.2	27-14-11-25
eClass 7.1	27-14-11-25		

Approvals

Approvals



ROHS	Conform
------	---------

Datenblatt

P-series
PDL 4/L/L/PE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

