

Zack marker strip - ZB 5,LGS:L1-N,PE - 1050415

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Zack marker strip, Strip, white, labeled, Horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, Mounting type: Snap into tall marker groove, For terminal block width: 5.2 mm, Lettering field: 5.15 x 10.5 mm

The illustration shows a combination of versions, ZB 5 UNPRINTED, ZB 5 SO/CMS, as well as ZB 5 LGS- ZB 7,5 LGS CONSEC.NOS

Product Features

- Other pitches available on request
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required
- Unlabeled marking strips can be custom-labeled with a plotter or by hand
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

Key commercial data

package_quantity	10
GTIN	4017918015701

Technical data

Dimensions

Width (a)	5 mm
------------------	------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 100 °C

General

Note	10 identically marked strips make up one packing unit (PU).
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Printing direction	Horizontal
Printing	L1, L2, L3, N, PE, L1, L2, L3, N, PE
Number of individual labels	10
Number of individual labels per row	10

Zack marker strip - ZB 5,LGS:L1-N,PE - 1050415

Technical data

General

Number of marker strips	10
--------------------------------	----

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Drawings