

# Connection terminal block - PTI 4 - 3213970

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Connection terminal block, Push-in connection, Cross section: 0.2 mm<sup>2</sup> - 6 mm<sup>2</sup>, AWG: 24 - 10, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

## Product Features

- Compatible with all Phoenix Contact installation terminal blocks
- Each terminal point can be clearly labeled and easily recognized in every terminal block mounting position
- As well as the testing facility in the function shaft, each terminal point has a test contact
- Compact design tailored to installation distributors
- The new Push-in connection technology enables easy, direct insertion of solid and stranded conductors with ferrules with a cross section of 0.34 mm<sup>2</sup> or higher

## Key commercial data

<b>package_quantity</b>	50
<b>GTIN</b>	4046356609296

## Technical data

### General

<b>Number of levels</b>	1
<b>Number of connections</b>	2
<b>Color</b>	gray
<b>Insulating material</b>	PA
<b>Inflammability class according to UL 94</b>	V0

### General

<b>Maximum load current</b>	32 A (with 6 mm <sup>2</sup> conductor cross section)
<b>Rated surge voltage</b>	6 kV
<b>Pollution degree</b>	3
<b>Surge voltage category</b>	III
<b>Insulating material group</b>	I
<b>Connection in acc. with standard</b>	IEC 60947-7-1
<b>Nominal current I<sub>N</sub></b>	32 A
<b>Nominal voltage U<sub>N</sub></b>	800 V
<b>Open side panel</b>	ja
<b>Shock protection test specification</b>	DIN EN 50274 (VDE 0660-514):2002-11
<b>Back of the hand protection</b>	guaranteed

# Connection terminal block - PTI 4 - 3213970

## Technical data

### General

Finger protection	guaranteed
Surge voltage test setpoint	9.8 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	2 kV
Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test rotation speed	10 rpm
Bending test turns	135
Bending test conductor cross section/weight	0.2 mm <sup>2</sup> / 0.2 kg
Bending test conductor cross section/weight	4 mm <sup>2</sup> / 0.9 kg
Bending test conductor cross section/weight	6 mm <sup>2</sup> / 1.4 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.2 mm <sup>2</sup>
Tractive force setpoint	10 N
Conductor cross section tensile test	4 mm <sup>2</sup>
Tractive force setpoint	60 N
Conductor cross section tensile test	6 mm <sup>2</sup>
Tractive force setpoint	80 N
Tensile test result	Test passed
Tight fit on carrier	NS 35
Setpoint	1 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	4 mm <sup>2</sup>
Short-time current	0.48 kA
Conductor cross section short circuit testing	6 mm <sup>2</sup>
Short-time current	0.72 kA
Short circuit stability result	Test passed
Ageing test for screwless modular terminal block temperature cycles	192
Result of aging test	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 2, bogie mounted
Test frequency	f <sub>1</sub> = 5 Hz to f <sub>2</sub> = 250 Hz
ASD level	6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz
Acceleration	3.12 g

# Connection terminal block - PTI 4 - 3213970

## Technical data

### General

Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Oscillation, broadband noise test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	30 g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Shock test result	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Static insulating material application in cold	-60 °C

### Dimensions

Width	6.2 mm
Length	66 mm
Height	42.50 mm
Height NS 35/7,5	44 mm
Height NS 35/15	51.5 mm

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	6 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm <sup>2</sup>
Connection method	Push-in connection
Stripping length	12 mm
Internal cylindrical gage	A4

# Connection terminal block - PTI 4 - 3213970

## Technical data

### classifications

#### eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

#### ETIM

ETIM 4.0	EC000897
ETIM 5.0	EC000897

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410


### approvals

---

GOST / GL /

---

#### Approval details



### accessories

#### End cover

D-DTI 4 - 3034895



# Connection terminal block - PTI 4 - 3213970

## accessories

---

DP PS-6 - 3036738



## Partition plate

---

ATP-PTI/3 - 3213990



## Screwdriver tools

---

SZF 1-0,6X3,5 - 1204517



## Support

---

AB-PTI - 3214006



## Documentation

---

# Connection terminal block - PTI 4 - 3213970

accessories

PT-IL - 3208090



---

## Bridge

FBS 20-6 - 3030365



---

FBS 10-6 - 3030271



---

FBS 5-6 - 3030349



---

FBS 4-6 - 3030255



## Connection terminal block - PTI 4 - 3213970

### accessories

FBS 3-6 - 3030242



FBS 2-6 - 3030336



FBS 50-6 - 3032224



### Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



## Connection terminal block - PTI 4 - 3213970

### accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762





## Connection terminal block - PTI 4 - 3213970

accessories

---

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



## Connection terminal block - PTI 4 - 3213970

### accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



# Connection terminal block - PTI 4 - 3213970

accessories

---

## Terminal marking

ZBF 5:UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



## Connection terminal block - PTI 4 - 3213970

### accessories

UCT-TM 6 - 0828736



ZBF 6:UNBEDRUCKT - 0808710



UC-TMF 6 - 0818140



UCT-TMF 6 - 0828746



TMT 6 R - 0816498



TMT (EX9,5)R - 0828295



# Connection terminal block - PTI 4 - 3213970

accessories

---

## Labeled terminal marker

ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



## Connection terminal block - PTI 4 - 3213970

### accessories

UCT-TM 6 CUS - 0829602



ZBF 6 CUS - 0825027



UC-TMF 6 CUS - 0824646



UCT-TMF 6 CUS - 0829665



TMT 6 R CUS - 0824488



**Test plug terminal block**

## Connection terminal block - PTI 4 - 3213970

### accessories

MPS-MT - 0201744



PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



## Connection terminal block - PTI 4 - 3213970

### accessories

---

PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-6 - 3030996





# Connection terminal block - PTI 4 - 3213970

## accessories

PS-6/2,3MM RD - 3038736



---

### Insulating sleeve

MPS-IH WH - 0201663



---

MPS-IH RD - 0201676



---

MPS-IH BU - 0201689



---

MPS-IH YE - 0201692



## Connection terminal block - PTI 4 - 3213970

### accessories

MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



ISH 4/0,5 - 3002885



ISH 4/1,0 - 3002898



### Planning and marking software

## Connection terminal block - PTI 4 - 3213970

### accessories

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



### End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



### Drawings

## Connection terminal block - PTI 4 - 3213970

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>