

# Interface module - UM 45-D 9SUB/S - 2962777

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and D-subminiature pin strip, for assembly on NS 35/7.5, 9 positions

The illustration shows the version UM 45-D37SUB/S



## Key commercial data

package_quantity	1
GTIN	4017918087432

## Technical data

### Dimensions

Width	54 mm
Height	45 mm
Depth	42 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

### General

Nominal voltage $U_N$	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
Max. current carrying capacity per branch	1.5 A (with even load on all branches)
Number of positions	9
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN VDE 110
Pollution degree	2
Surge voltage category	II
Rated surge voltage	1.2 kV
Rated insulation voltage	125 V

### Connection data for connection 1

# Interface module - UM 45-D 9SUB/S - 2962777

## Technical data

### Connection data for connection 1

<b>Connection name</b>	PCB connection
<b>Connection in acc. with standard</b>	IEC / EN
<b>Connection method</b>	Screw connection
<b>Conductor cross section solid min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	1.5 mm <sup>2</sup>
<b>Conductor cross section stranded min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	1.5 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	26
<b>Conductor cross section AWG/kcmil max</b>	16
<b>Stripping length</b>	6 mm
<b>Screw thread</b>	M3

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27250313
<b>eCl@ss 4.1</b>	27250313
<b>eCl@ss 5.0</b>	27250313
<b>eCl@ss 5.1</b>	27250313
<b>eCl@ss 6.0</b>	27242608
<b>eCl@ss 7.0</b>	27141152
<b>eCl@ss 8.0</b>	27141152

### ETIM

<b>ETIM 2.0</b>	EC001434
<b>ETIM 3.0</b>	EC001604
<b>ETIM 4.0</b>	EC001604
<b>ETIM 5.0</b>	EC002780

### UNSPSC

<b>UNSPSC 6.01</b>	30211824
<b>UNSPSC 7.0901</b>	39121421
<b>UNSPSC 11</b>	39121421
<b>UNSPSC 12.01</b>	39121421
<b>UNSPSC 13.2</b>	39121421

## approvals

---

UL Recognized / cUL Recognized / GOST / cULus Recognized /

---

### Approval details

# Interface module - UM 45-D 9SUB/S - 2962777

## approvals

<b>UL Recognized</b>	
Nominal voltage UN	125 V
Nominal current IN	2.5 A
mm <sup>2</sup> /AWG/kcmil	30-14

<b>cUL Recognized</b>	
Nominal voltage UN	125 V
Nominal current IN	2.5 A
mm <sup>2</sup> /AWG/kcmil	30-14

<b>GOST</b>
-------------

<b>cULus Recognized</b>
-------------------------

## accessories

### System cable

CABLE-D 9SUB/B/S/ 50/KONFEK/S - 2299987



CABLE-D 9SUB/B/S/100/KONFEK/S - 2299990



## Interface module - UM 45-D 9SUB/S - 2962777

### accessories

CABLE-D 9SUB/B/S/150/KONFEK/S - 2300009



CABLE-D 9SUB/B/S/200/KONFEK/S - 2302010



CABLE-D 9SUB/B/S/300/KONFEK/S - 2302023



CABLE-D 9SUB/B/S/400/KONFEK/S - 2302036



CABLE-D 9SUB/B/S/600/KONFEK/S - 2302049



CABLE D-SUB-S/.../.../... - 2302340



## Interface module - UM 45-D 9SUB/S - 2962777

### accessories

---

CABLE D-SUB-B-B-S/.../.../... - 2302421



CABLE-D- 9SUB/F/OE/0,25/S/0,5M - 2926014



CABLE-D- 9SUB/F/OE/0,25/S/1,0M - 2926027



CABLE-D- 9SUB/F/OE/0,25/S/1,5M - 2926030



CABLE-D- 9SUB/F/OE/0,25/S/2,0M - 2926043



## Interface module - UM 45-D 9SUB/S - 2962777

### accessories

CABLE-D- 9SUB/F/OE/0,25/S/3,0M - 2926056



CABLE-D- 9SUB/F/OE/0,25/S/4,0M - 2926069



CABLE-D- 9SUB/F/OE/0,25/S/6,0M - 2926072




CABLE-D- 9SUB-F-OE-0,25-S/... - 2900903



### Drawings

# Interface module - UM 45-D 9SUB/S - 2962777

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>