

# Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 5, Pitch: 5 mm, Connection method: Screw connection, Color: green, Contact surface: Tin

## Product Features

- Plug-in direction parallel to the conductor axis
- Standard plug-in system for 320 V (III/2)
- Individual position coding by inserting coding profiles

## Key commercial data

<b>package_quantity</b>	50
<b>GTIN</b>	4017918028671

## Technical data

### Dimensions

<b>Pitch</b>	5 mm
<b>Dimension a</b>	20 mm

### General

<b>Range of articles</b>	MSTB 2,5/..-ST
<b>Insulating material group</b>	I
<b>Rated surge voltage (III/3)</b>	4 kV
<b>Rated surge voltage (III/2)</b>	4 kV
<b>Rated surge voltage (II/2)</b>	4 kV
<b>Rated voltage (III/3)</b>	250 V
<b>Rated voltage (III/2)</b>	320 V
<b>Rated voltage (II/2)</b>	630 V
<b>Connection in acc. with standard</b>	EN-VDE
<b>Nominal current I<sub>N</sub></b>	12 A
<b>Nominal cross section</b>	2.5 mm <sup>2</sup>
<b>Maximum load current</b>	12 A (with 2.5 mm <sup>2</sup> conductor cross section)
<b>Insulating material</b>	PA
<b>Inflammability class according to UL 94</b>	V0
<b>Internal cylindrical gage</b>	A3
<b>Stripping length</b>	7 mm
<b>Number of positions</b>	5

# Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504

## Technical data

### General

<b>Screw thread</b>	M3
<b>Tightening torque, min</b>	0.5 Nm
<b>Tightening torque max</b>	0.6 Nm

### Connection data

<b>Conductor cross section solid min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section stranded min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve min.</b>	0.25 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve min.</b>	0.25 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	24
<b>Conductor cross section AWG/kcmil max</b>	12
<b>2 conductors with same cross section, solid min.</b>	0.2 mm <sup>2</sup>
<b>2 conductors with same cross section, solid max.</b>	1 mm <sup>2</sup>
<b>2 conductors with same cross section, stranded min.</b>	0.2 mm <sup>2</sup>
<b>2 conductors with same cross section, stranded max.</b>	1.5 mm <sup>2</sup>
<b>2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.</b>	0.25 mm <sup>2</sup>
<b>2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.</b>	1 mm <sup>2</sup>
<b>2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.</b>	0.5 mm <sup>2</sup>
<b>2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.</b>	1.5 mm <sup>2</sup>
<b>Minimum AWG according to UL/CUL</b>	30
<b>Maximum AWG according to UL/CUL</b>	12

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	272607xx
<b>eCl@ss 4.1</b>	27260701
<b>eCl@ss 5.0</b>	27260701
<b>eCl@ss 5.1</b>	27260701
<b>eCl@ss 6.0</b>	27260704
<b>eCl@ss 7.0</b>	27440402
<b>eCl@ss 8.0</b>	27440402

# Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504

## classifications

### ETIM

<b>ETIM 3.0</b>	EC001121
<b>ETIM 4.0</b>	EC002638
<b>ETIM 5.0</b>	EC002638

### UNSPSC

<b>UNSPSC 6.01</b>	30211810
<b>UNSPSC 7.0901</b>	39121409
<b>UNSPSC 11</b>	39121409
<b>UNSPSC 12.01</b>	39121409
<b>UNSPSC 13.2</b>	39121409

## approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / IECEE CB Scheme / GOST / CCA / cULus Recognized /

### Approval details

<b>CSA</b>		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm <sup>2</sup> /AWG/kcmil	28-12	28-12

<b>UL Recognized</b>		
Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	10 A
mm <sup>2</sup> /AWG/kcmil	30-12	30-12

<b>VDE Gutachten mit Fertigungsüberwachung</b>	
Nominal voltage UN	250 V
Nominal current IN	12 A
mm <sup>2</sup> /AWG/kcmil	0.2-2.5

# Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504

## approvals

**cUL Recognized**

Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	10 A
mm <sup>2</sup> /AWG/kcmil	30-12	30-12

**GOST**

**IECEE CB Scheme**

Nominal voltage UN	250 V
Nominal current IN	12 A
mm <sup>2</sup> /AWG/kcmil	0.2-2.5

**CCA**

Nominal voltage UN	250 V
Nominal current IN	12 A
mm <sup>2</sup> /AWG/kcmil	0.2-2.5

**cULus Recognized**

## accessories

### Screwdriver tools

SZS 0,6X3,5 - 1205053



## Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504

accessories

---

### Labeled terminal marker

SK 5/3,8:FORTL.ZAHLEN - 0804183



### Cable housing

KGG-MSTB 2,5/ 5 - 1803895



### Coding element

CP-MSTB - 1734634



### Bridge

EBP 2- 5 - 1733169




### Drawings

# Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504


Diagram

Plug: FKIC 2,5/5-ST(F)(-5,08)  
Header: MSTB 2,5/5-ST(F)(-5,08)



Diagram


Plug: MSTB 2,5/5-ST(F)(-5,08)  
Header: SMSTB(A) 2,5/5-G(-5,08)



# Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504


Diagram

Plug: MSTB 2,5/5-ST(F)-(-5,08)  
Header: MDSTB 2,5/5-G(F)-(-5,08)




Diagram

Plug: MSTB 2,5/5-ST(F)-(-5,08)  
Header: MSTB(A) 2,5/5-G(F)-(-5,08)



# Printed-circuit board connector - MSTB 2,5/ 5-ST - 1754504

Diagram



Type: MSTB 2,5/...-ST with MSTBW 2,5/...-G

Dimensioned drawing

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>