

Feed-through terminal block - MT 1,5 BU - 3003363

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.14 mm² - 1.5 mm², AWG: 26 - 16, Width: 4.2 mm, Color: blue, Mounting type: NS 15

Product Features

- Nominal cross section of 1.5 mm²
- Space saving thanks to compact design and mounting option on a 15 mm DIN rail
- Clear arrangement thanks to marking of all terminal points
- Easy potential distribution thanks to standardized plug-in bridges
- Design width of just 4.2 mm
- Wide range of labeling options
- Snap-on foot for NS 15 DIN rails
- Can be bridged in terminal center

Key commercial data

package_quantity	50
GTIN	4017918107086

Technical data

General

Number of levels	1
Number of connections	2
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Rated surge voltage	4 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	17.5 A
Nominal voltage U _N	400 V
Open side panel	ja

Feed-through terminal block - MT 1,5 BU - 3003363

Technical data

Dimensions

Width	4.2 mm
Length	22 mm
Height NS 15	23.5 mm

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	26
Max. AWG conductor cross section, stranded	16
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	0.75 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	0.75 mm ²
2 conductors with same cross section, solid min.	0.14 mm ²
2 conductors with same cross section, solid max.	0.5 mm ²
2 conductors with same cross section, stranded min.	0.14 mm ²
2 conductors with same cross section, stranded max.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	0.34 mm ²
Connection method	Screw connection
Stripping length	6 mm
Internal cylindrical gage	A 1
Screw thread	M2
Tightening torque, min	0.22 Nm
Tightening torque max	0.25 Nm

classifications

eCl@ss

eCl@ss 4.0	27141123
eCl@ss 4.1	27141123
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120

Feed-through terminal block - MT 1,5 BU - 3003363

classifications

eCl@ss

eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / KEMA-KEUR / GOST / LR / GL / BV / DNV / CCA / GOST /

Approval details

Nominal voltage UN	300 V
Nominal current IN	15 A
mm ² /AWG/kcmil	28-14

Nominal voltage UN	300 V
Nominal current IN	15 A
mm ² /AWG/kcmil	30-14

Nominal voltage UN	400 V

Feed-through terminal block - MT 1,5 BU - 3003363

approvals

Nominal current I _N	
mm ² /AWG/kcmil	1.5




LR

GL

BV

DNV

CCA	
Nominal voltage U _N	400 V
Nominal current I _N	
mm ² /AWG/kcmil	1.5



accessories

End cover

D-MT 1,5 BU - 3025529



Screwdriver tools

Feed-through terminal block - MT 1,5 BU - 3003363

accessories

SZS 0,4X2,5 VDE - 1205037



Bridge

FBRN 8-4 N - 3001608



FBRN 7-4 N - 3001598



FBRN 6-4 N - 3001585



FBRN 5-4 N - 3001572



Feed-through terminal block - MT 1,5 BU - 3003363

accessories

FBRN 4-4 N - 3001569



FBRN 20-4 N - 3001637



FBRN 10-4 N - 3001624



Mounting rail

NS 15 UNPERF 2000MM - 1401695



NS 15 PERF 2000MM - 1401682



Feed-through terminal block - MT 1,5 BU - 3003363

accessories

NS 15 AL PERF 2000MM - 1401763



NS 15 WH PERF 2000MM - 1204096



Terminal marking

ZBF 4:UNBEDRUCKT - 0808587



UC-TMF 4 - 0818166



UCT-TMF 4 - 0828742



Labeled terminal marker

Feed-through terminal block - MT 1,5 BU - 3003363

accessories

ZBF 4 CUS - 0825023



UC-TMF 4 CUS - 0824630



UCT-TMF 4 CUS - 0829651



End block

E/MBK - 1401637



E/MK - 1421633



Feed-through terminal block - MT 1,5 BU - 3003363

accessories

E/MK 1 - 1421659



accessories

FBRN 9-4 N - 3001611

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>