

GB

Page 1 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 21.08.2015 / 0009
Replacing version dated / version: 22.10.2012 / 0008
Valid from: 21.08.2015
PDF print date: 25.08.2015
Lederpflege 250 mL
Art.: 1554

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Lederpflege 250 mL
Art.: 1554

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture:

Care components
Sector of use [SU]:
SU 3 - Industrial uses: Uses of substances as such or in preparations at industrial sites
SU21 - Consumer uses: Private households (=general public = consumers)
SU22 - Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
Chemical product category [PC]:
PC31 - Polishes and wax blends
PC35 - Washing and cleaning products (including solvent based products)
Process category [PROC]:
PROC 8a - Transfer of substance or preparation (charging/discharging) from/to vessels/large containers at non-dedicated facilities
PROC 9 - Transfer of substance or preparation into small containers (dedicated filling line, including weighing)
PROC10 - Roller application or brushing
Article Categories [AC]:
AC99 - Not required.
Environmental Release Category [ERC]:
ERC 4 - Industrial use of processing aids in processes and products, not becoming part of articles
ERC 8a - Wide dispersive indoor use of processing aids in open systems
ERC 8d - Wide dispersive outdoor use of processing aids in open systems

Uses advised against:

No information available at present.

1.3 Details of the supplier of the safety data sheet

GB

LIQUI MOLY GmbH, Jerg-Wieland-Str. 4, 89081 Ulm-Lehr, Germany
Phone: (+49) 0731-1420-0, Fax: (+49) 0731-1420-88

Qualified person's e-mail address: info@chemical-check.de, k.schnurbusch@chemical-check.de Please DO NOT use for requesting Safety Data Sheets.

1.4 Emergency telephone number

Emergency information services / official advisory body:

Telephone number of the company in case of emergencies:

+49 (0) 700 / 24 112 112 (LMR)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) 1272/2008 (CLP)

The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

2.2 Label elements

Labeling according to Regulation (EC) 1272/2008 (CLP)

GB

Page 2 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0009
 Replacing version dated / version: 22.10.2012 / 0008
 Valid from: 21.08.2015
 PDF print date: 25.08.2015
 Lederpflege 250 mL
 Art.: 1554

Not applicable

2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006.

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006.

REGULATION (EC) No 648/2004

less than 5 %
 non-ionic surfactants
 polycarboxylates

perfumes
 BUTYLPHENYL METHYLPROPIONAL
 COUMARIN
 HYDROXYISOHEXYL 3-CYCLOHEXENE CARBOXALDEHYDE
 LINALOOL
 BENZISOTHIAZOLINONE
 METHYLISOTHIAZOLINONE

SECTION 3: Composition/information on ingredients

3.1 Substance

n.a.

3.2 Mixture

--	
Registration number (REACH)	--
Index	-
EINECS, ELINCS, NLP	-
CAS	-
content %	
Classification according to Regulation (EC) 1272/2008 (CLP)	---

SECTION 4: First aid measures

4.1 Description of first aid measures

Inhalation

Supply person with fresh air and consult doctor according to symptoms.

Skin contact

Wash thoroughly with soap and water.
 Remove contaminated clothing immediately.

Eye contact

Remove contact lenses.
 Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Rinse the mouth thoroughly with water.
 Give copious water to drink - consult doctor immediately.

4.2 Most important symptoms and effects, both acute and delayed

Irritation of the eyes

In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

4.3 Indication of any immediate medical attention and special treatment needed

n.c.

SECTION 5: Firefighting measures

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 21.08.2015 / 0009

Replacing version dated / version: 22.10.2012 / 0008

Valid from: 21.08.2015

PDF print date: 25.08.2015

Lederpflege 250 mL

Art.: 1554

5.1 Extinguishing media

Suitable extinguishing media

Adapt to the nature and extent of fire.

Unsuitable extinguishing media

n.c.

5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Oxides of carbon

Silicon dioxide

Oxides of nitrogen

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes.

Protective respirator with independent air supply.

Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Avoid contact with eyes.

If applicable, caution - risk of slipping.

6.2 Environmental precautions

If leakage occurs, dam up.

Resolve leaks if this possible without risk.

Prevent surface and ground-water infiltration, as well as ground penetration.

Do not pour down the drain undiluted.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth, sawdust) and dispose of according to Section 13.

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Avoid contact with eyes.

Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.

Observe directions on label and instructions for use.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.

Store product closed and only in original packing.

Protect from frost.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Page 4 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0009
 Replacing version dated / version: 22.10.2012 / 0008
 Valid from: 21.08.2015
 PDF print date: 25.08.2015
 Lederpflege 250 mL
 Art.: 1554

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.
 If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.
 Applies only if maximum permissible exposure values are listed here.

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.
 Wash hands before breaks and at end of work.
 Keep away from food, drink and animal feedingstuffs.
 Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:
 Tight fitting protective goggles (EN 166) with side protection, with danger of projections.

Skin protection - Hand protection:
 Rubber gloves (EN 374).
 Protective hand cream recommended.
 The breakthrough times determined in accordance with EN 374 Part 3 were not obtained under practical conditions.
 The recommended maximum wearing time is 50% of breakthrough time.

Skin protection - Other:
 Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments).

Respiratory protection:
 Normally not necessary.

Thermal hazards:
 Not applicable

Additional information on hand protection - No tests have been performed.
 In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.
 Selection of materials derived from glove manufacturer's indications.
 Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.
 Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.
 In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.
 The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Light, Beige
Odour:	Mild
Odour threshold:	Not determined
pH-value:	7 (20°C)
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	100 °C
Flash point:	n.a.
Evaporation rate:	Not determined
Flammability (solid, gas):	n.a.
Lower explosive limit:	Not determined
Upper explosive limit:	Not determined
Vapour pressure:	23 hPa (20°C)
Vapour density (air = 1):	Not determined
Density:	1 g/cm ³ (20°C)
Bulk density:	n.a.

(GB)

Page 5 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0009
 Replacing version dated / version: 22.10.2012 / 0008
 Valid from: 21.08.2015
 PDF print date: 25.08.2015
 Lederpflege 250 mL
 Art.: 1554

Solubility(ies):	Not determined
Water solubility:	Dispersion
Partition coefficient (n-octanol/water):	Not determined
Auto-ignition temperature:	No
Decomposition temperature:	Not determined
Viscosity:	Not determined
Explosive properties:	Product is not explosive.
Oxidising properties:	Not determined
9.2 Other information	
Miscibility:	Not determined
Fat solubility / solvent:	Not determined
Conductivity:	Not determined
Surface tension:	Not determined
Solvents content:	0 %

SECTION 10: Stability and reactivity

10.1 Reactivity

The product has not been tested.

10.2 Chemical stability

Stable with proper storage and handling.

10.3 Possibility of hazardous reactions

No dangerous reactions are known.

10.4 Conditions to avoid

See also section 7.

None known

10.5 Incompatible materials

None known

10.6 Hazardous decomposition products

See also section 5.2

No decomposition when used as directed.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Possibly more information on health effects, see Section 2.1 (classification).

Lederpflege 250 mL

Art.: 1554

Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:	t					n.d.a.
Acute toxicity, by dermal route:						n.d.a.
Acute toxicity, by inhalation:						n.d.a.
Skin corrosion/irritation:						n.d.a.
Serious eye damage/irritation:						n.d.a.
Respiratory or skin sensitisation:						n.d.a.
Germ cell mutagenicity:						n.d.a.
Carcinogenicity:						n.d.a.
Reproductive toxicity:						n.d.a.
Specific target organ toxicity - single exposure (STOT-SE):						n.d.a.
Specific target organ toxicity - repeated exposure (STOT-RE):						n.d.a.
Aspiration hazard:						n.d.a.
Symptoms:						n.d.a.
Other information:						Classification according to calculation procedure.

SECTION 12: Ecological information

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0009
 Replacing version dated / version: 22.10.2012 / 0008
 Valid from: 21.08.2015
 PDF print date: 25.08.2015
 Lederpflege 250 mL
 Art.: 1554

Possibly more information on environmental effects, see Section 2.1 (classification).

Lederpflege 250 mL							
Art.: 1554							
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
Toxicity to fish:							n.d.a.
Toxicity to daphnia:							n.d.a.
Toxicity to algae:							n.d.a.
Persistence and degradability:							The surfactant(s) contained in this mixture complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.
Bioaccumulative potential:							n.d.a.
Mobility in soil:							n.d.a.
Results of PBT and vPvB assessment							n.d.a.
Other adverse effects:							n.d.a.
Other information:							According to the recipe, contains no AOX.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2014/955/EU)

07 06 99 wastes not otherwise specified

Recommendation:

Sewage disposal shall be discouraged.

Pay attention to local and national official regulations.

E.g. dispose at suitable refuse site.

For contaminated packing material

Pay attention to local and national official regulations.

Empty container completely.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

Uncontaminated packaging can be recycled.

Recommended cleaner:

Water

Cleaning product

SECTION 14: Transport information

General statements

UN number:

n.a.

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 21.08.2015 / 0009

Replacing version dated / version: 22.10.2012 / 0008

Valid from: 21.08.2015

PDF print date: 25.08.2015

Lederpflege 250 mL

Art.: 1554

Transport by road/by rail (ADR/RID)

UN proper shipping name:

Transport hazard class(es): n.a.

Packing group: n.a.

Classification code: n.a.

LQ (ADR 2015): n.a.

Environmental hazards: Not applicable

Tunnel restriction code:

Transport by sea (IMDG-code)

UN proper shipping name:

Transport hazard class(es): n.a.

Packing group: n.a.

Marine Pollutant: n.a.

Environmental hazards: Not applicable

Transport by air (IATA)

UN proper shipping name:

Transport hazard class(es): n.a.

Packing group: n.a.

Environmental hazards: Not applicable

Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

Transport in bulk according to Annex II of MARPOL and the IBC Code

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

For classification and labelling see Section 2.

Observe restrictions:

General hygiene measures for the handling of chemicals are applicable.

Directive 2010/75/EU (VOC): 0 %

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

Revised sections:

1 - 16

Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

The following phrases represent the posted Hazard Class and Risk Category Code (GHS/CLP) of the product and the constituents (specified in Section 2 and 3).

Any abbreviations and acronyms used in this document:

AC Article Categories

acc., acc. to according, according to

ACGIH American Conference of Governmental Industrial Hygienists

ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)

AOEL Acceptable Operator Exposure Level

AOX Adsorbable organic halogen compounds

approx. approximately

Page 8 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0009
 Replacing version dated / version: 22.10.2012 / 0008
 Valid from: 21.08.2015
 PDF print date: 25.08.2015
 Lederpflege 250 mL
 Art.: 1554

Art., Art. no.	Article number
ATE	Acute Toxicity Estimate according to Regulation (EC) 1272/2008 (CLP)
BAM	Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)
BAuA	Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)
BCF	Bioconcentration factor
BGV	Berufsgenossenschaftliche Vorschrift (= Accident Prevention Regulation)
BHT	Butylhydroxytoluol (= 2,6-Di-t-butyl-4-methyl-phenol)
BMGV	Biological monitoring guidance value (EH40, UK)
BOD	Biochemical oxygen demand
BSEF	Bromine Science and Environmental Forum
bw	body weight
CAS	Chemical Abstracts Service
CEC	Coordinating European Council for the Development of Performance Tests for Fuels, Lubricants and Other Fluids
CESIO	Comité Européen des Agents de Surface et de leurs Intermédiaires Organiques
CIPAC	Collaborative International Pesticides Analytical Council
CLP	Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)
CMR	carcinogenic, mutagenic, reproductive toxic
COD	Chemical oxygen demand
CTFA	Cosmetic, Toiletry, and Fragrance Association
DMEL	Derived Minimum Effect Level
DNEL	Derived No Effect Level
DOC	Dissolved organic carbon
DT50	Dwell Time - 50% reduction of start concentration
DVS	Deutscher Verband für Schweißen und verwandte Verfahren e.V. (= German Association for Welding and Allied Processes)
dw	dry weight
e.g.	for example (abbreviation of Latin 'exempli gratia'), for instance
EC	European Community
ECHA	European Chemicals Agency
EEA	European Economic Area
EEC	European Economic Community
EINECS	European Inventory of Existing Commercial Chemical Substances
ELINCS	European List of Notified Chemical Substances
EN	European Norms
EPA	United States Environmental Protection Agency (United States of America)
ERC	Environmental Release Categories
ES	Exposure scenario
etc.	et cetera
EU	European Union
EWG	European Waste Catalogue
Fax.	Fax number
gen.	general
GHS	Globally Harmonized System of Classification and Labelling of Chemicals
GWP	Global warming potential
HET-CAM	Hen's Egg Test - Chorionallantoic Membrane
HGWP	Halocarbon Global Warming Potential
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IBC	Intermediate Bulk Container
IBC (Code)	International Bulk Chemical (Code)
IC	Inhibitory concentration
IMDG-code	International Maritime Code for Dangerous Goods
incl.	including, inclusive
IUCLID	International Uniform Chemical Information Database
LC	lethal concentration
LC50	lethal concentration 50 percent kill
LCLo	lowest published lethal concentration
LD	Lethal Dose of a chemical
LD50	Lethal Dose, 50% kill
LDLo	Lethal Dose Low
LOAEL	Lowest Observed Adverse Effect Level
LOEC	Lowest Observed Effect Concentration
LOEL	Lowest Observed Effect Level
LQ	Limited Quantities

Page 9 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 21.08.2015 / 0009
Replacing version dated / version: 22.10.2012 / 0008
Valid from: 21.08.2015
PDF print date: 25.08.2015
Lederpflege 250 mL
Art.: 1554

MARPOL International Convention for the Prevention of Marine Pollution from Ships
n.a. not applicable
n.av. not available
n.c. not checked
n.d.a. no data available
NIOSH National Institute of Occupational Safety and Health (United States of America)
NOAEC No Observed Adverse Effective Concentration
NOAEL No Observed Adverse Effect Level
NOEC No Observed Effect Concentration
NOEL No Observed Effect Level
ODP Ozone Depletion Potential
OECD Organisation for Economic Co-operation and Development
org. organic
PAH polycyclic aromatic hydrocarbon
PBT persistent, bioaccumulative and toxic
PC Chemical product category
PE Polyethylene
PNEC Predicted No Effect Concentration
POCP Photochemical ozone creation potential
ppm parts per million
PROC Process category
PTFE Polytetrafluorethylene
REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)
REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.
RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)
SADT Self-Accelerating Decomposition Temperature
SAR Structure Activity Relationship
SU Sector of use
SVHC Substances of Very High Concern
Tel. Telephone
ThOD Theoretical oxygen demand
TOC Total organic carbon
TRGS Technische Regeln für Gefahrstoffe (=Technical Regulations for Hazardous Substances)
UN RTDG United Nations Recommendations on the Transport of Dangerous Goods
VbF Verordnung über brennbare Flüssigkeiten (= Regulation for flammable liquids (Austria))
VOC Volatile organic compounds
vPvB very persistent and very bioaccumulative
WEL-TWA, WEL-STEL WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period), WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period) (EH40, UK).
WHO World Health Organization
wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.
No responsibility.

These statements were made by:

Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.