

# KERN 572-57

Allrounder z. B. als Präzisionswaage im Labor oder im rauen Industrieinsatz



## Functions

Conversion function:	yes
Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Suspended weighing:	Loop
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

## Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

## Service

DAkkS Certificate:	963-128
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	400 x 340 x 220 mm
Gross weight:	4,800 kg
Net weight:	2,700 kg
Shipping method:	Parcel service

## Construction

Casing material:	Cast aluminium alloys
Dimensions housing (WxDxH):	180 x 310 x 85 mm
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	180 x 310 x 90 mm
Weighing surface (WxD):	160 x 200 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
n/a:	200 g
Readout [d]:	100 mg
Recommended adjusting weight:	20 kg (F1)
Reproducibility:	100 mg
Resolution:	240000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	24 kg
Weighing system:	Strain gauge
Weighing units:	ct dwt g gn kg lb mo oz t tl (Cn) tl (HK) tl (Singap. Malays) tl (Tw) to

## Display

Display digit height:	1,800 cm
-----------------------	----------

## Counting

Counting resolution:	240000
Minimum piece weight at piece counting (Laboratory):	100 mg
Minimum piece weight at piece counting (Normal):	1 g