

Feed-through terminal block - ST 1,5 BU - 3031089

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Spring-cage connection, Cross section: 0.08 mm² - 1.5 mm², AWG: 28 - 16, Width: 4.2 mm, Color: blue, Mounting type: NS 35/7,5, NS 35/15

The illustration shows version ST 1,5 in gray

Product Features

- The consistent double function shaft offers every opportunity for time-saving potential distribution and accommodating test accessories
- Tested for railway applications
- As well as saving space, the compact design and front connection enable user-friendly wiring in a small amount of space
- The large wiring space enables the use of conductors with ferrules and plastic collars within the nominal cross section



Key commercial data

package_quantity	50
GTIN	4017918186630

Technical data

General

Number of levels	1
Number of connections	2
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering
Area of application	Process industry

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III

Feed-through terminal block - ST 1,5 BU - 3031089

Technical data

General

Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I_N	17.5 A
Nominal voltage U_N	500 V
Open side panel	ja

Dimensions

Width	4.2 mm
Length	48.5 mm
Height NS 35/7,5	36.5 mm
Height NS 35/15	44 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	28
Max. AWG conductor cross section, stranded	16
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Stripping length	10 mm
Internal cylindrical gage	A 1

classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120

Feed-through terminal block - ST 1,5 BU - 3031089

classifications

eCl@ss

eCl@ss 8.0	27141120
------------	----------

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / LR / GL / BV / DNV / KR / NK / IECB Scheme / GOST / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	440 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	0.08-1.5

ATEX	
Nominal voltage UN	440 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	0.08-1.5

CSA		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm ² /AWG/kcmil	26-14	26-14

Feed-through terminal block - ST 1,5 BU - 3031089

approvals

UL Recognized

Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm ² /AWG/kcmil	26-14	26-14

VDE Gutachten mit Fertigungsüberwachung

Nominal voltage UN	500 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	1.5

cUL Recognized

Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm ² /AWG/kcmil	26-14	26-14

GOST

LR

GL

Nominal voltage UN	500 V
Nominal current IN	17.5 A
mm ² /AWG/kcmil	1.5

BV


DNV

KR

Feed-through terminal block - ST 1,5 BU - 3031089

approvals

NK

IECEE CB Scheme 	
Nominal voltage UN	500 V
Nominal current IN	
mm ² /AWG/kcmil	1.5



cULus Recognized 

accessories

End cover

D-ST 2,5 - 3030417



D-ST 2,5-0,8 OG - 3030511



DP PS-4 - 3036712



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

Test plug terminal block

RPS - 0201647



MPS-MT - 0201744



PAI-4 - 3030925



PS-4 - 3030970



Partition plate

ATP-ST 4 - 3030721



Screwdriver tools

Feed-through terminal block - ST 1,5 BU - 3031089

accessories

SZF 0-0,4X2,5 - 1204504



Labeled terminal marker

WST 1,5 - 3030958



ZB 4 CUS - 0824951



UC-TM 4 CUS - 0824573



UCT-TM 4 CUS - 0829588



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

ZBF 4 CUS - 0825023



UC-TMF 4 CUS - 0824630



UCT-TMF 4 CUS - 0829651



Documentation

ST-IL - 3039900



Bridge

FBS 20-4 - 3030352



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

FBS 10-4 - 3030158



FBS 4-4 - 3030132



FBS 3-4 - 3030129



FBS 2-4 - 3030116



FBS 5-4 - 3030145



Mounting rail

Feed-through terminal block - ST 1,5 BU - 3031089

accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 4 :UNBEDRUCKT - 0805001



UC-TM 4 - 0818111



UCT-TM 4 - 0828732



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

ZBF 4:UNBEDRUCKT - 0808587



UC-TMF 4 - 0818166



UCT-TMF 4 - 0828742



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



ISH 1,5/0,2 - 3206131



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

ISH 1,5/0,5 - 3031034



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



Feed-through terminal block - ST 1,5 BU - 3031089

accessories

E/UK 1 - 1201413



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>