

# KERN CM320-1N

Die Praktische mit Klappdeckel



## Category

Brand:	KERN
Category:	Balances
Product Group:	Pocket balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	140 x 200 x 30 mm
Gross weight:	318 g
Net weight:	216 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	85 x 130 x 25 mm
Material weighing plate:	Plastic
Weighing surface (WxD):	70 x 80 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	200 mg
Readout [d]:	100 mg
Recommended adjusting weight:	200 g (M3)
Reproducibility:	100 mg
Resolution:	3200
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	320 g
Weighing system:	Strain gauge
Weighing units:	g tl (Tw) tol

## Display

Display digit height:	1,200 cm
-----------------------	----------

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Operating time:	70 h
-----------------	------

## Service

Adjustment at the location of installation: 961-247

DAkKS Certificate: 963-127