


The H-DD series with machined crimp contacts - for a high number of pin in very tight spaces.

Product Description

The H-DD series with machined contacts is designed for a high number of pins in very tight spaces. This allows for smaller housing types to be chosen.



Application range

- Mechanical engineering
- Light & sound technology
- Plastics industry

Benefits

- The H-DD series with machined contacts is designed for a high number of pins in very tight spaces. This allows for smaller housing types to be chosen.



Technical Data

Rated voltage (V)

IEC: 250 V UL: 600 V CSA: 600 V

Rated impulse voltage

2.5 kV

Rated current (A)

IEC: 10 A UL: 8.5 A CSA: 10 A

Contact resistance

< 3 mOhm

Contacts

Copper alloy, hard silver/gold-plated

Number of contacts

24 + PE

Termination methods

Crimp termination: 0.14 - 2.5 mm²

Cycle of mechanical operation

100

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

VDE-tested

Certified production control: VDE-REG. no. 437

Degree of soiling

2

Article List

Part number	Article	Version	Article designation	Contacts	Pieces / PU
H-DD 24 crimp termination					
11285000	H-DD 24 SCM	male	machined	1 - 24	5
11286000	H-DD 24 BCM	female	machined	1 - 24	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.