

SAUTER FH 5



Universal digital force gauge for tensile and compressive force measurements with integrated load cell



Material display housing	plastic
Mounting - force application	External thread M6
Load support (tensile force)	Hook

Functions	
Function for averaging	✓
Limit-setting function	✓
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min

Interface	
Interfaces	RS-232 standard USB-Device

Power Supply	
Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH

Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	5 V 1000 mA
Power socket for mains adapter	USB C
Battery / accumulator type	NiMH
Battery connection	2-pole tub connector
Battery capacity	1.200 mAh
Battery voltage	3,7 V
Battery - Number of cells	3
Battery - Construction	Inseparable connection of cells (pack)
Battery capacity (Wh)	4,4 Wh
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	40 h
Rechargeable battery charging time	120 min
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions	
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C

Category	
Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge (internal measuring cell)
Product family	FH-S

Measuring System	
Measuring range force [Max] (N)	5 N
Readability force [d] (N)	0,001 N
Measuring head measuring frequency	2 kHz
Internal data memory: Number of value groups	1
Overload protection (% of [Max])	150%
Tolerance (% of [Max])	0,5%
Internal data memory: Number of individual values	10
Directions of force	tension compression
Default unit	N

Display	
Display type	LCD
Screen reversible	✓

Construction	
Dimension housing (W×D×H)	230×70×40 mm
Dimensions completely mounted (W×D×H)	280×70×40 mm
Dimension display device (W×D×H)	240×70×40 mm
Material housing	plastic

SAUTER FH 5



Universal digital force gauge for tensile and compressive force measurements with integrated load cell

Storage temperature [Min]	-10 °C
---------------------------	--------

Storage temperature [Max]	40 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Services (optional)

Article number for factory calibration (tensile force)	961-161
--	---------

Article number for factory calibration (compressive force)	961-261
--	---------

Article number for factory calibration (tensile force/ compressive force)	961-361
--	---------

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	330×190×95 mm
------------------------------	---------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	0,55 kg
--------------------	---------

Gross weight approx.	1,4 kg
----------------------	--------

Shipping weight	1,287 kg
-----------------	----------

Product information

GTIN/EAN number	4045761368576
-----------------	---------------

REACH classification	no prohibited substances
----------------------	--------------------------

Pictograms

STANDARD



OPTION

