

Accessories ZB 4K GE/GN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com



In the switching facilities and controllers, the N conductor may need to be merged with the PE conductor at a central point. For this reason, busbars are available that allow a wide range of cables to be connected within a confined space (up to 70 wires on one metre of rail). The cables are connected via a compression piece or a clamping yoke. For the first variant there is no need to bend the lugs. A guide lug at the compression piece grips into the busbar and holds tightly to the compression piece. The clamping yokes can be moved on the busbar and adjusted to the whole wiring in the facility. The busbar can be used without holes in various lengths. The rail holding clamp SH is used for fastening. On longer rails, it can also be aligned between clamping yokes.

General ordering data

Туре	ZB 4K GE/GN
Order No.	<u>0475360000</u>
Version	Accessories, Clamping yoke for busbar, Rated cross-section: Clamping yoke, PA, green / yellow
GTIN (EAN)	4008190188047
Qty.	50 pc(s).



Accessories ZB 4K GE/GN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083

www.weidmueller.com

Technische Daten

Dimensions and weights

Dimensions and weights				
Length	20 mm	Width	6 mm	
Height of lowest version	19 mm	Net weight	3.72 g	
Temperatures				
Operating temperature		Storage temperature		
Rated data IECEx/ATEX				
ATEX certificate	DEMK003ATEX136028U_d.	NATEV contificato	DEMKO03ATEX136028U_e.p	
Voltage, cross-connection	DLIVIKOUSATEX 1300280_u.	Operating temperature range	For operating temperature	
voltage, cross commoditori		oporating comporation range	range see EC Design Test Certificate / IEC Ex-	
Moulsing ATEX Discotive 04/0/EC	CrossConnectionGuide.pdf II 2 G D		Certificate of Conformity	
Marking ATEX Directive 94/9/EC	II 2 G D			
Additional technical data				
Version	15 x 6 mm busbar connection			
CSA ratings data				
Certificate No. (CSA)	12400-237	Wire cross section max. (CSA)	10 AWG	
Wire cross section min. (CSA)	26 AWG	Wife closs section max. (CSA)	10 AVVG	
Clampable wires (rated conne	ction)			
Type of connection	Clamping yoke	Tightening torque, min.	1.2 Nm	
Wire connection cross section, solid		Wire connection cross section, solid		
core, max. rated connection	0.5 mm ²	core max. rated connection 6 m		
Wire connection cross section, finely stranded, max.	Wire connection cross-section, finely 4 mm ² stranded, min.		0.5 mm ²	
Dimensions				
TS 35 offset	39 mm			
UL ratings data				
Contificate No. (LID)	T60602	Conductor size Footomy vising many /IID)	12 11/0	
Certificate No. (UR) Conductor size Factory wiring min. (UR)	E60693 20 AWG	Conductor size Factory wiring max. (UR) Conductor size Field wiring max. (UR)	12 AWG	
Material data	20700	Conductor Size Field Willing Hax. (Off)	127770	
la sulatio a se stadial	DA	Material	Charl	
Insulating material Colour	PA Silver	Material	Steel	
System specifications	Olivoi			
System specifications				
Product family	Accessories	Type of connection	Clamping yoke	
Mounting rail	TS 35			



Accessories ZB 4K GE/GN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Technische Daten

Classifications

ETIM 3.0	EC00001	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-31	eClass 6.2	27-14-11-90
eClass 7.1	27-14-11-90		

Rated data IECEx/ATEX

Safety notice

Installation instructions:

The potential equalisation (PE) rail modules are suitable for use in housings in atmospheres with flammable gases and dust. For use in areas with flammable gases, these housings must meet the requirements of EN 60079-0 and EN 60079-7. For use in areas with flammable dust, these housings must meet the requirements of EN 60079-0 and EN 60079-31.

When combined with other terminal block ranges and sizes, and when other accessories are used, you must comply with the clearance and creepage distances given.

Regarding accessory use, the manufacturer's instructions must be followed.

List of restrictions:

The PE rail modules are considered one component, with Ex marking when used with the busbar holders of type SH and WEW. When used independently, the above named components are not covered by this certificate.

Approvals

Approvals



ROHS Conform