



|   |   |
|---|---|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 255-406/000-009/999-950                   |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.5 - 2.5                                 |
| <b>Cross section2 (Cross section / AWG)</b>                 | 20 - 12                                   |
| <b>Strip length (Strip length / mm)</b>                     | 5 - 6                                     |
| <b>Measured voltage (Measured voltage / V)</b>              | 275                                       |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> |   |
| <b>Pollution degree (Pollution degree)</b>                  |   |
| <b>Current intensity (Current intensity / A)</b>            | 16  |
| <b>RM (PIN SPACING / mm)</b>                                | 5   |
| <b>P (NO. OF POLES)</b>                                     | 6   |
| <b>Height (Height / mm)</b>                                 | 14.2                                      |
| <b>Width (Width / mm)</b>                                   | 32.9                                      |
| <b>Depth (Depth / mm)</b>                                   | 18.3                                      |
| <b>No. of connection Points (No. of connection Points)</b>  | 6   |
| <b>No. of potentials (No. of potentials)</b>                | 6   |
| <b>COLOR (COLOR)</b>  | lichtgrau                                 |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 7.1                                       |
| <b>Comment (Comment)</b>                                    | L = (No. of poles x Pin Spacing) + 2,9 mm |
| <b>Dimensions (Dimensions)</b>                              | 1,1 + 0,1 mm                              |