

KERN HFB 300K100

Die professionelle Alternative bis 600 kg mit rückwärtiger Zweitanzeige



n/a: Mains adapter external

Power supply

Operating time (Backlight off): 40 h

Operating time (Backlight on): 30 h

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129H

Category

Brand: KERN

Category: Balances

Product Group: Crane scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 435 x 255 x 210 mm

Gross weight: 3,200 kg

Net weight: 2,200 kg

Shipping method: Parcel service

UN number: 2800

Construction

Casing material: Plastic

Dimensions of display device (WxDxH): 163 x 126 x 160 mm

Overall dimensions mounted (WxDxH): 163 x 126 x 410 mm

Measuring system

Adjustment options: External calibration

Linearity: 200 g

Precision (of [Max]): 0,002

Readout [d]: 100 g

Recommended adjusting weight: 300 kg (M3)

Reproducibility: 100 g

Resolution: 3000

Stabilisation time: 2 s

Tare range: -300000000 mg

Warm up time: 10 min

Weighing range [Max]: 300 kg

Weighing system: Strain gauge

Weighing units: kg lb

Display

Additional Display possible: no

Display digit height: 2,500 cm

Functions

Data hold function: yes

Environmental conditions

Maximum humidity: 85 %

Maximum operating temperature: 40 °C

Minimum ambient temperature: 0 °C

Minimum humidity: 0 %

Power supply

Charging time: 14 h

Input voltage: 220 V - 240 V AC 50 Hz

n/a: CH EURO UK