

KERN HFM10T1

Industrie-Kranwaage bis 10 Tonnen

KERN[®]



Measuring system

Adjustment options:	External calibration
Linearity:	10 kg
Precision (of [Max]):	0,002
Readout [d]:	1 kg
Recommended adjusting weight:	10000 kg (M1)
Reproducibility:	5 kg
Resolution:	10000
Stabilisation time:	2 s
Tare range:	10 t
Warm up time:	30 min
Weighing range [Max]:	10 t
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	3 cm
-----------------------	------

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Charging time:	14 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	50 h
Operating time (Backlight on):	50 h

Service

Adjustment at the location of installation: 961-252

DAkkS Certificate:	963-133H
ISO calibration certificate:	961-106

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

KERN HFM10T1

Industrie-Kranwaage bis 10 Tonnen



Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	800 x 395 x 470 mm
Gross weight:	38,400 kg
Net weight:	34 kg
Shipping method:	Parcel service
UN number:	2800

Construction

Casing material:	Cast aluminium alloys
Dimensions of display device (WxDxH):	300 x 190 x 230 mm
Overall dimensions mounted (WxDxH):	300 x 190 x 840 mm