

# KERN KB 120-3N

Kompakte Präzisionswaage mit großem Wägebereich, auch mit Eichzulassung [M]



## Measuring system

Adjustment options:	External calibration
Linearity:	3 mg
n/a:	2 g
Readout [d]:	1 mg
Recommended adjusting weight:	100 g (F1)
Reproducibility:	1 mg
Resolution:	120000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	120 g
Weighing system:	Strain gauge
Weighing units:	ct dwt g gn kg lb mo oz t tl (Cn) tl (HK) tl (Singap. Malays) tl (Tw) to

## Display

Display digit height:	9 mm
-----------------------	------

## Counting

Counting resolution:	120000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

## Functions

Conversion function:	yes
Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Suspended weighing:	Hook
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

## Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

## Service

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	238 x 357 x 180 mm
Gross weight:	2,200 kg
Net weight:	1 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions draft shield (ÅxH):	106   42
Dimensions housing (WxDxH):	167 x 250 x 85 mm
Overall dimensions mounted (WxDxH):	167 x 250 x 123 mm

# KERN KB 120-3N



Kompakte Präzisionswaage mit großem Wägebereich, auch mit Eichzulassung [M]

Weighing space (ÅxH): 90 | 40

Weighing surface (d): 81