

Interface module - FLKM-D25 SUB/B - 2281209

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and D-Subminiature socket strip, for mounting on NS 35/7.5 or NS 32, 25-pos.

The illustration shows version
FLKM-D37 SUB/S



Key commercial data

package_quantity	5
GTIN	4017918054632

Technical data

Dimensions

Width	78.8 mm
Height	77 mm
Depth	58.5 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
Max. current carrying capacity per branch	1.5 A (with even load on all branches)
Number of positions	25
Status display	No
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2
Surge voltage category	II
Rated surge voltage	1.2 kV

Interface module - FLKM-D25 SUB/B - 2281209

Technical data

General

Rated insulation voltage	125 V
---------------------------------	-------

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

Interface module - FLKM-D25 SUB/B - 2281209

approvals

Approval details

UL Recognized 	
Nominal voltage UN	125 V
Nominal current IN	2.5 A
mm²/AWG/kcmil	30-12

cUL Recognized 	
Nominal voltage UN	125 V
Nominal current IN	2.5 A
mm²/AWG/kcmil	30-12

GOST 	
--	--

cULus Recognized 	
--	--

accessories

System cable

CABLE-D25SUB/B/S/ 50/KONFEK/S - 2302120



CABLE-D25SUB/B/S/100/KONFEK/S - 2302133



Interface module - FLKM-D25 SUB/B - 2281209

accessories

CABLE-D25SUB/B/S/150/KONFEK/S - 2302146



CABLE-D25SUB/B/S/200/KONFEK/S - 2302159



CABLE-D25SUB/B/S/300/KONFEK/S - 2302162



CABLE-D25SUB/B/S/400/KONFEK/S - 2302175



CABLE-D25SUB/B/S/600/KONFEK/S - 2302188



CABLE D-SUB-S/.../.../... - 2302340



Interface module - FLKM-D25 SUB/B - 2281209

accessories

CABLE D-SUB-S-S/.../.../... - 2302434



CABLE-D-25SUB/M/OE/0,25/S/0,5M - 2926506



CABLE-D-25SUB/M/OE/0,25/S/1,0M - 2926519



CABLE-D-25SUB/M/OE/0,25/S/1,5M - 2926522



CABLE-D-25SUB/M/OE/0,25/S/2,0M - 2926535



Interface module - FLKM-D25 SUB/B - 2281209

accessories

CABLE-D-25SUB/M/OE/0,25/S/3,0M - 2926548



CABLE-D-25SUB/M/OE/0,25/S/4,0M - 2926551



CABLE-D-25SUB/M/OE/0,25/S/6,0M - 2926564



CABLE-D-25SUB-M-OE-0,25-S/... - 2900911



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>