

KERN TE1250-0.1F.

Ergonomisches Design und externer Messkopf für höchsten Bedienkomfort



Packaging & shipping

| | |
|-------------------------------|-------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 265 x 215 x 63 mm |
| Gross weight: | 660 g |
| Net weight: | 85 g |
| Shipping method: | Parcel service |

Construction

| | |
|-------------------------------------|------------------|
| Casing material: | Plastic |
| Overall dimensions mounted (WxDxH): | 131 x 65 x 28 mm |

Measuring system

| | |
|--|--------------------------|
| Measuring range [Max]: | 100 x 1250 μm |
| Minimal base thickness: | 300 μm |
| Precision (of [Max]): | 3 % |
| Precision (Offset-Accur): | 1 % |
| Readout [d]: | 0 x 0,001 mm |
| Smallest sample surface, flat (radius): | 1,500 mm |
| Smallest sample surface, concave (radius): | 2,500 cm |
| Weighing units: | μm inch (mil) |

Display

| | |
|-----------------------|------|
| Display digit height: | 1 cm |
|-----------------------|------|

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum operating temperature: | 50 °C |
| Minimum ambient temperature: | 0 °C |

Power supply

| | |
|-----------------|------|
| Operating time: | 50 h |
|-----------------|------|

Service

| | |
|------------------------------|---------|
| ISO calibration certificate: | 961-110 |
|------------------------------|---------|

Category

| | |
|----------------|-------------------------|
| Brand: | Sauter |
| Category: | Coating thickness |
| Product Group: | Coating thickness gauge |