

QT-ECO 1X26/220...240 S

QUICKTRONIC ECONOMIC | ECG for FL 7 mm and CFL



Areas of application

- Public buildings

Product benefits

- Compact housing
- Automatic restart after lamp replacement

Product features

- Supply voltage: 220...240 V
- Line voltage: 198...264 V
- Line frequency: 50 Hz | 60 Hz
- Energy Efficiency Index EEI: A2
- Automatic shutdown of defective lamps and at end of life (EoL)

Product datasheet

Technical data

Electrical data


Nominal voltage	220...240 V
Mains frequency	50 Hz
DC voltage	176...254 V
Operating frequency	35...45 kHz
Max. no. of ECGs on circuit breaker 10 A	30
Max. no. of ECGs on circuit breaker 16 A	50

Light technical data

Starting time	1.5 s ¹⁾
---------------	---------------------

¹⁾ Preheat start: After a switch off, the lamps should remain switched off for 2 minutes to ensure an optimum preheat start

Dimensions & weight



Product line drawing

Length	80.0 mm
Width	40.0 mm
Height	22.0 mm
Mounting hole spacing, length	72.0...75.0 mm
Product weight	50.00 g

Temperatures

Ambient temperature range	-15...+50 °C
---------------------------	--------------

Capabilities

Dimmable	No
----------	----









Product datasheet

Suitable for fixtures with prot. class	I / II
End of lamp life safety shutdown	EOL T.2

Certificates & standards

Approval marks – approval	VDE
EEL – Energy Label	A3
Standards	acc. to EN 61347-2-3/acc. to EN 55015:2006 + A1:2007/acc. to EN 61000-3-2/acc. to EN 61547

Download Data

File
 Certificates VDE-Marks approval
 Certificates VDE-Marks approval
 Certificates Manufacturer's declaration EN 55015:2006+A1:2007 (300 MHz)
 Declarations of conformity Declaration of conformity
 CAD data 3-dim 80x40x22 9900019
 CAD data 3-dim 80x40x22 9900019
 CAD data 3-dim 80x40x22 9900019
 CAD data PDF 80x40x22 9900019

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321065971	QT-ECO 1X26/220...240 S	Shipping carton box 50	170 mm x 142 mm x 212 mm	5.12 dm ³	2791.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

Product datasheet

Lamp-ECG combination (System)

Product name	Lamp group	Nominal current	Nominal wattage + Power loss	Luminous flux at 25 °C	Number of lighting outlets
QT-ECO 1x26/220-240 S	DULUX D/E 26 W XT	0.18 A	23.50 W	1600 lm	1
	DULUX D/E 26 W	0.18 A	23.50 W	1600 lm	1
	DULUX T/E 26 W	0.18 A	23.50 W	1600 lm	1