

# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/M12FS - 1681619

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator cable, 5-position, PUR halogen-free, Black-gray RAL 7021, Plug straight M12, A-coded, on Socket straight M12, A-coded, Cable length: 3 m

## Product Features

- Easy and safe: 100% electrically tested plug-in components
- Our standard: robust halogen-free PUR cable

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918158101

## Technical data

### Dimensions

<b>Length of cable</b>	3 m
------------------------	-----

### Ambient conditions

<b>Ambient temperature (operation)</b>	-25 °C ... 90 °C (Plug / socket)
<b>Degree of protection</b>	IP65
<b>Degree of protection</b>	IP67
<b>Degree of protection</b>	IP68

### General

<b>Rated current at 40°C</b>	4 A
<b>Rated voltage</b>	60 V
<b>Number of positions</b>	5
<b>Contact resistance</b>	≤ 5 mΩ
<b>Insulation resistance</b>	≥ 100 MΩ
<b>Coding</b>	A - standard
<b>Standards/regulations</b>	M12 connector IEC 61076-2-101
<b>Status display</b>	No
<b>Protective circuit/component</b>	Unwired
<b>Surge voltage category</b>	II
<b>Pollution degree</b>	3
<b>Insertion/withdrawal cycles</b>	≥ 100

# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

## Technical data

### General

<b>Torque</b>	0.4 Nm (M12 connector)
---------------	------------------------

### Material

<b>Inflammability class according to UL 94</b>	HB
<b>Contact material</b>	CuSn
<b>Contact surface material</b>	Ni/Au
<b>Contact carrier material</b>	TPU GF
<b>Material of grip body</b>	TPU, hardly inflammable, self-extinguishing
<b>Material, knurls</b>	Zinc die-cast, nickel-plated
<b>Sealing material</b>	NBR

### Cable

<b>Cable type</b>	PUR halogen-free black
<b>Cable type (abbreviation)</b>	PUR
<b>UL AWM style</b>	20549
<b>Conductor cross section</b>	5x 0.34 mm <sup>2</sup> (signal line)
<b>AWG signal line</b>	22
<b>Conductor structure signal line</b>	42x 0.10 mm
<b>Core diameter including insulation</b>	1.27 mm ±0.02 mm (signal line)
<b>Thickness, insulation</b>	approx. 0.7 mm
<b>Wire colors</b>	brown, white, blue, black, green-yellow
<b>External sheath, color</b>	Black-gray RAL 7021
<b>External cable diameter D</b>	5 mm ±0.15 mm
<b>Smallest bending radius, fixed installation</b>	25 mm
<b>Smallest bending radius, movable installation</b>	50 mm
<b>Number of bending cycles</b>	4000000
<b>Bending radius</b>	50 mm
<b>Traversing path</b>	10 m
<b>Traversing rate</b>	3 m/s
<b>Acceleration</b>	10 m/s <sup>2</sup>
<b>Cable weight</b>	35 kg/km
<b>Outer sheath, material</b>	PUR
<b>Conductor material</b>	Bare Cu litz wires
<b>Insulation resistance</b>	≥ 16 GΩ*km (at 20 °C)
<b>Conductor resistance</b>	max. 58 Ω/km (at 20 °C)
<b>Nominal voltage, cable</b>	300 V
<b>Test voltage, cable</b>	3000 V
<b>Special properties</b>	Flexible cable conduit capable
<b>Special properties</b>	Silicone-free
<b>Special properties</b>	Free of substances which would hinder coating with paint or varnish

# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

## Technical data

### Cable

<b>Special properties</b>	Flexible
<b>Flame resistance</b>	in accordance with DIN UL-Style 20549
<b>Halogen-free</b>	in accordance with DIN VDE 0472 part 815
<b>Resistance to oil</b>	in accordance with DIN EN 60811-2-1
<b>Other resistance</b>	Highly resistant to acids, alkaline solutions and solvents
<b>Other resistance</b>	hydrolysis and microbe resistant
<b>Other resistance</b>	Resistant to salt water
<b>Other resistance</b>	partly UV-resistant in accordance with DIN EN ISO 4892-2-A
<b>Ambient temperature (operation)</b>	-40 °C ... 80 °C (cable, fixed installation)
<b>Ambient temperature (operation)</b>	-25 °C ... 80 °C (cable, flexible installation)

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27061801
<b>eCl@ss 6.0</b>	27061801
<b>eCl@ss 7.0</b>	27061801
<b>eCl@ss 8.0</b>	27061801

### ETIM

<b>ETIM 2.0</b>	EC000830
<b>ETIM 3.0</b>	EC001855
<b>ETIM 4.0</b>	EC001855
<b>ETIM 5.0</b>	EC001855

### UNSPSC

<b>UNSPSC 6.01</b>	31251501
<b>UNSPSC 7.0901</b>	31251501
<b>UNSPSC 11</b>	31251501
<b>UNSPSC 12.01</b>	31251501
<b>UNSPSC 13.2</b>	31251501

## approvals

---

UL Listed / cUL Listed / GOST / cULus Listed /

---

### Approval details

# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

approvals

<b>UL Listed</b>	
Nominal voltage UN	125 V
Nominal current IN	4 A
mm <sup>2</sup> /AWG/kcmil	

<b>cUL Listed</b>	
Nominal voltage UN	125 V
Nominal current IN	4 A
mm <sup>2</sup> /AWG/kcmil	

<b>GOST</b>	
-------------	--

<b>cULus Listed</b>	
---------------------	--

accessories

## Protective cap

PROT-M12 FS-PA-CHAIN - 1430873



PROT-M12 MS-PA-CHAIN - 1430899



## Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

accessories

### Safety locking

SAC-M12-EXCLIP-M - 1558988



SAC-M12-EXCLIP-F - 1558991



### Conductor marking

PABA WH/15 - 1013151



PABA YE/15 - 1013698



PABA RD/15 - 1013944



## Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

accessories

### Marker carrier cable

PATO 2/15 - 1013122



PATO 3/15 - 1013135



PATO 4/15 - 1013148



### Marker pen

B-STIFT - 1051993



### Torque tool

TSD 04 SAC - 1208429



# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

accessories

---

TSD-M 1,2NM - 1212224



## Screwdriver tools

---

TSD-M SAC-BIT ADAPTER - 1212600




SAC BIT M12-D15 - 1208432



## Drawings


Dimensioned drawing



M12 x 1 plug, straight

# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

Dimensioned drawing



M12 x 1 socket, straight

Circuit diagram




Contact assignment of the M12 plug and the M12 socket



# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619


Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

# Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619


Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

## Sensor/Actuator cable - SAC-5P-M12MS/3,0-PUR/ M12FS - 1681619

Cable cross section



PUR halogen-free black [PUR]

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>