

# KERN 440-35A

Der Klassiker im Labor

# KERN®



## Measuring system

Adjustment options:	External calibration
Linearity:	30 mg
n/a:	20 g
Readout [d]:	10 mg
Recommended adjusting weight:	500 g (F2)
Reproducibility:	10 mg
Resolution:	60000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	600 g
Weighing system:	Strain gauge
Weighing units:	ct dwt g gn lb mo oz ozt tl (HK) tl (Tw) tol

## Display

Display digit height:	1,500 cm
-----------------------	----------

## Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	20 mg
Minimum piece weight at piece counting (Normal):	200 mg

## Functions

Counting function:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Charging time:	10 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK US
Operating time:	12 h
Operating time (Backlight off):	20 h
Rechargeable battery:	Rchrg. battery optional

## Service

Adjustment at the location of installation:	961-247
DAkkS Certificate:	963-127

## Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	345 x 215 x 170 mm
Gross weight:	1,380 kg
Net weight:	959 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	165 x 230 x 80 mm
Material weighing plate:	stainless steel
Weighing surface (d):	110