

KERN 572-30

Allrounder z. B. als Präzisionswaage im Labor oder im rauen Industrieinsatz



Functions

Conversion function:	yes
Counting function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Suspended weighing:	Loop
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

Service

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Precision balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	400 x 340 x 220 mm
Gross weight:	4,400 kg
Net weight:	2,300 kg
Shipping method:	Parcel service

Construction

Casing material:	metal
Dimensions housing (WxDxH):	180 x 310 x 85 mm
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	180 x 310 x 130 mm

Measuring system

Adjustment options:	External calibration
Linearity:	3 mg
n/a:	2 g
Readout [d]:	1 mg
Recommended adjusting weight:	200 g (F1)
Reproducibility:	1 mg
Resolution:	240000
Stabilisation time:	3 s
Warm up time:	2 h
Weighing range [Max]:	240 g
Weighing system:	Strain gauge
Weighing units:	ct dwt g gn kg lb mo oz t tl (Cn) tl (HK) tl (Singap. Malays) tl (Tw) to

Display

Display digit height:	1,800 cm
-----------------------	----------

Counting

Counting resolution:	240000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

KERN 572-30



Allrounder z. B. als Präzisionswaage im Labor oder im rauen Industrieinsatz

Weighing space (ÅxH): 157 | 43

Weighing surface (d): 106