


SAUTER AC 17

Long clamp for tension and rupture tests

KERN



Pictograms

STANDARD



Category

Brand	Sauter
Product category	Clamp
Product group	Screw tension clamp

Measuring System

Directions of force	tension
---------------------	---------

Construction

Dimensions completely mounted (W×D×H)	8×40×18,5 mm
Material	steel
Mounting - force dissipation	Threaded hole M6
Maximum clamp width	8 mm
Clamping width	2,5 mm
Tensile/compressive force [Max]	500 N

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	150×100×10 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg

Product information

GTIN/EAN number	4045761122406
REACH classification	no prohibited substances