

# Passive module - FLKMS 50/32IM/LA/PLC - 2284510

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE sensor module, for connecting 32 p-n-p sensors, with LED

## Product Features

- With LED as an option
- For 32 channels
- Byte-by-byte labeling
- Positive and negative connection per signal



## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918055684

## Technical data

### Dimensions

<b>Width</b>	180 mm
<b>Height</b>	90 mm
<b>Depth</b>	81 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 50 °C
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C

### General

<b>Nominal voltage <math>U_N</math></b>	20 V DC (up to 30 V DC)
<b>Max. current carrying capacity per branch</b>	1 A
<b>Max. total current of voltage supply</b>	2 A (per byte)
<b>Number of positions</b>	50
<b>Status display</b>	LED
<b>Test voltage</b>	500 V (50 Hz, 1 min.)
<b>Mounting position</b>	Any
<b>Standards/regulations</b>	IEC 60664
<b>Standards/regulations</b>	DIN EN 50178

# Passive module - FLKMS 50/32IM/LA/PLC - 2284510

## Technical data

### General

<b>Standards/regulations</b>	IEC 62103
<b>Pollution degree</b>	2
<b>Surge voltage category</b>	II
<b>Rated surge voltage</b>	0.8 kV

### Connection data for connection 1

<b>Connection name</b>	Field level
<b>Connection in acc. with standard</b>	IEC / EN
<b>Connection method</b>	Screw connection
<b>Conductor cross section solid min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	4 mm <sup>2</sup>
<b>Conductor cross section stranded min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	24
<b>Conductor cross section AWG/kcmil max</b>	12
<b>Stripping length</b>	8 mm
<b>Screw thread</b>	M3

### Connection data for connection 2

<b>Connection name</b>	Control system level
<b>Number of connections</b>	1
<b>Connection method</b>	IDC/FLK pin strip (2.54 mm)
<b>Number of positions</b>	50

### Supported controller

<b>Control</b>	SIEMENS S7-400
- suitable I/O card	6ES7 421-1BL01-0AA0
- suitable I/O card	6ES7 422-1BL00-0AA0
- suitable I/O card	6ES7 422-7BL00-0AB0
<b>Control</b>	ALLEN-BRADLEY ControlLogix
- suitable I/O card	1756-IB32
- suitable I/O card	1756-OB32
<b>Control</b>	ALLEN-BRADLEY PLC 5
- suitable I/O card	1771 IBN
- suitable I/O card	1771 OBN
<b>Control</b>	HONEYWELL PlantScape
- suitable I/O card	TC-IDD 321
- suitable I/O card	TC-ODD 321
<b>Control</b>	MITSUBISHI MELSEC L
- suitable I/O card	LX41C4
- suitable I/O card	LX42C4
- suitable I/O card	LY41NT1P
- suitable I/O card	LY42NT1P

## Passive module - FLKMS 50/32IM/LA/PLC - 2284510

### Technical data

#### Supported controller

- suitable I/O card	LY41PT1P
- suitable I/O card	LY42PT1P
<b>Control</b>	MITSUBISHI MELSEC Q
- suitable I/O card	QX81
- suitable I/O card	QY81P
- suitable I/O card	QX41
- suitable I/O card	QX41-S1
- suitable I/O card	QX42
- suitable I/O card	QX42-S1
- suitable I/O card	QY41P
- suitable I/O card	QY42P
- suitable I/O card	QH42P
- suitable I/O card	QX82
- suitable I/O card	QX82-S1
<b>Control</b>	Schneider Electric MODICON TSX QUANTUM
- suitable I/O card	DDI 353
- suitable I/O card	DDI 853
- suitable I/O card	DDO 353
<b>Control</b>	SIEMENS S7-300 / ET 200 M
- suitable I/O card	CPU 313C-2DP
- suitable I/O card	CPU 314C-2DP
- suitable I/O card	CPU 314C-2PtP
- suitable I/O card	6ES7 321-1BL00-0AA0
- suitable I/O card	6ES7 322-1BL00-0AA0
- suitable I/O card	6ES7 323-1BL00-0AA0
- suitable I/O card	CPU 313C
- suitable I/O card	CPU 313C-2PtP
<b>Control</b>	GE-FANUC RX3i
- suitable I/O card	IC694MDL754
- suitable I/O card	IC694MDL660

### classifications

#### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27371601
eCl@ss 7.0	27371601
eCl@ss 8.0	27371601

# Passive module - FLKMS 50/32IM/LA/PLC - 2284510

## classifications

### ETIM

ETIM 2.0	EC001437
ETIM 3.0	EC001437
ETIM 4.0	EC001437
ETIM 5.0	EC001437



### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /


### Approval details



## Drawings

# Passive module - FLKMS 50/32IM/LA/PLC - 2284510

Circuit diagram



FLKMS 50/32IM/LA/PLC connection scheme

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>