

KERN CM60-2N

Die Praktische mit Klappdeckel

KERN®



Category

Brand:	KERN
Category:	Balances
Product Group:	Pocket balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	135 x 205 x 32 mm
Gross weight:	306 g
Net weight:	180 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	85 x 130 x 25 mm
Material weighing plate:	Plastic
Weighing surface (WxD):	70 x 80 mm

Measuring system

Adjustment options:	External calibration
Linearity:	30 mg
Readout [d]:	10 mg
Recommended adjusting weight:	50 g (M2)
Reproducibility:	20 mg
Resolution:	6000
Stabilisation time:	2 s
Warm up time:	30 min
Weighing range [Max]:	60 g
Weighing system:	Strain gauge
Weighing units:	g tl (Tw) tol

Display

Display digit height:	1,200 cm
-----------------------	----------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Operating time:	30 h
-----------------	------

Service

Adjustment at the location of installation: 961-247

DAkKS Certificate: 963-127