



Discover more details and matching accessories online!

The classic balance with robust tuning fork measuring system

Features

- **1** KERN EG: Internal adjustment in the case of a change in temperature and time-controlled at defined intervals, guarantees high degree of accuracy and makes the balance independent of its location of use
- Stable temperature behaviour
- Short stabilisation time
- Shock proof construction
- High corner load performance

- Capacity display: A bargraph display lights up to show how much of the weighing range is still available
- Totalising of pieces when counting
- **A** Draught shield standard for models with weighing plate size **A**, weighing space W×D×H 158×130×78 mm
- Protective working cover included with delivery

Technical data

- Large LCD display, digit height 17 mm
- Dimensions weighing surface, stainless steel
A ø 118 mm, see larger picture
B W×D 170×140 mm
C W×D 180×160 mm
- Overall dimensions W×D×H
A 185×235×165 mm
B, C 180×235×75 mm
- Permissible ambient temperature 10 °C/30 °C

STANDARD



OPTION



FACTORY



Model	Weighing capacity [Max] g	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Linearity g	Weighing plate	Net weight kg	Options	
								Verification M KERN	Calibr. Certificate DAkkS accr. KERN
KERN									
EW 220-3NM	220	0,001	-	-	± 0,002	A	1,4	-	963-127
EW 420-3NM	420	0,001	-	-	± 0,003	A	1,4	-	963-127
EW 620-3NM	620	0,001	-	-	± 0,003	A	1,4	-	963-103
EW 820-2NM	820	0,01	-	-	± 0,01	B	1,6	-	963-127
EW 2200-2NM	2200	0,01	-	-	± 0,01	C	3,0	-	963-127
EW 4200-2NM	4200	0,01	-	-	± 0,02	C	3,0	-	963-127
EW 6200-2NM	6200	0,01	-	-	± 0,03	C	3,0	-	963-104
EW 12000-1NM	12000	0,1	-	-	± 0,2	C	3,0	-	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order.

The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

EG 220-3NM	220	0,001	0,01	0,02	± 0,002	A	2,0	965-216	963-127
EG 420-3NM	420	0,001	0,01	0,02	± 0,003	A	1,8	965-216	963-127
EG 620-3NM	620	0,001	0,01	0,1	± 0,004	A	2,0	965-201	963-103
EG 2200-2NM	2200	0,01	0,1	0,5	± 0,01	C	4,0	965-216	963-127
EG 4200-2NM	4200	0,01	0,1	0,5	± 0,02	C	4,0	965-216	963-127