

SAUTER FL 200

Universal digital force gauge with graphic-assisted display and integrated load cell

KERN



Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge
Product family	FL-S

Measuring System

Measuring range force [Max] (N)	250 N
Readability force [d] (N)	0,1 N
Measuring head measuring frequency	1000 Hz
Internal data memory: Number of value groups	1
Overload protection (% of [Max])	120%
Tolerance (% of [Max])	0,2%
Internal data memory: Number of individual values	500
Directions of force	tension compression
Default unit	N
Number of platforms / channels	1

Display

Display type	LCD
Display digit height	8,5 mm
Screen reversible	✓

Construction

Dimension housing (W×D×H)	175×75×30 mm
Dimensions completely mounted (W×D×H)	175×75×30 mm
Dimension display device (W×D×H)	175×75×30 mm

Material housing	metal, lacquered
Material display housing	aluminium
Mounting - force application	External thread M6
Load support (tensile force)	Hook

Functions

Limit-setting function	✓
Analogue signal	✓
Hold function	✓
Peak function	✓
Memory function	✓

Interface

Interfaces	RS-232 standard USB-Device analogue (0 +/-2V)
------------	---

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	9 V, 500 mA
Power socket for mains adapter	Hollow plug inside plus, Ø outside 5,5 mm; Ø inside 2,1 mm
Battery / accumulator type	NiMH
Battery capacity	750 mAh
Battery voltage	4,8 V
Battery - Individual weight	50 g
Rechargeable battery	4,8 V 750 mA
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	10 h
Rechargeable battery charging time	8 h
Battery/Accu connected	fixed electrical connection, not insulated

SAUTER FL 200

KERN

Universal digital force gauge with graphic-assisted display and integrated load cell

Environmental conditions

Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration (tensile force)	963-161
Article number for DAkkS calibration (compressive force)	963-261
Article number for DAkkS calibration (tensile force/ compressive force)	963-361
Article number for factory calibration (tensile force)	961-161
Article number for factory calibration (compressive force)	961-261
Article number for factory calibration (tensile force/ compressive force)	961-361

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	260×230×75 mm
Shipping method	Parcel service
Net weight approx.	0,55 kg
Gross weight approx.	1,4 kg
Shipping weight	1,386 kg

Product information

GTIN/EAN number	4045761138889
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

