

KERN HFM3T0.5

Industrie-Kranwaage bis 10 Tonnen

KERN[®]



Measuring system

Adjustment options:	External calibration
Linearity:	2 kg
Precision (of [Max]):	0,002
Readout [d]:	500 g
Recommended adjusting weight:	3000 kg (M1)
Reproducibility:	1 kg
Resolution:	6000
Stabilisation time:	2 s
Tare range:	-3000000000 mg
Warm up time:	30 min
Weighing range [Max]:	3 t
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height:	3 cm
-----------------------	------

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Charging time:	14 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	50 h
Operating time (Backlight on):	50 h

Service

Adjustment at the location of installation: 961-252

DAkkS Certificate:	963-132H
ISO calibration certificate:	961-105

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

KERN HFM3T0.5

Industrie-Kranwaage bis 10 Tonnen



Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	375 x 545 x 340 mm
Gross weight:	18 kg
Net weight:	15,700 kg
Shipping method:	Parcel service
UN number:	2800

Construction

Casing material:	Cast aluminium alloys
Dimensions of display device (WxDxH):	270 x 175 x 200 mm
Overall dimensions mounted (WxDxH):	270 x 175 x 610 mm