



Discover more details and matching accessories online!

Premium Leeb hardness tester – also with hardness comparison block included

Features

- External impact sensor standard (Type D)
- Mobility: In comparison with stationary table-top devices and testing devices with an internal sensor, using the SAUTER HK-D offers the highest level of mobility and flexibility
- All measurement directions possible (360°) thanks to an automatic compensation function
- 1 SAUTER HK-DB: Hardness comparison block, hardness approx. 800 HLD, included in delivery
- Measurement value display: Rockwell(Type A, B, C), Vickers (HV), Shore (HS), Leeb (HL), Brinell (HB)

- Internal memory for up to 600 data groups, with up to 32 values per group forming the average value of the group
- Mini statistics function: displays the measured result, the average value, the impact direction, date and time
- Automatic unit conversion:
The measuring result is automatically converted into all specified hardness units
- Measuring with tolerance range and programmable limit values. The process is supported by an audible and visual signal
- Matrix display: Backlit multi-function display
- Robust metal housing
- 2 Delivered in a robust carrying case

Technical data

- Precision: ± 1 % at 800 HLD
- Minimum sample radius (concave/convex): 50 mm (with support ring: 10 mm)
- Thinnest measurable material thickness: 3 mm, with coupling on fixed base
- The lowest weight of the test item on solid support unit: 2 kg with fixed coupling
- Battery operation, 2×1.5 V AA standard, operating time up to 200 h
- Permissible ambient temperature -10 °C/40 °C
- Overall dimensions W×D×H 132×82×31 mm

STANDARD



HK-DB

OPTION



HK-D

Model	Sensor	Measuring range	Readout	Test block	Net weight	Option
						Factory calibration certificate
SAUTER		HL	[d] HL	Typ D/DC approx. 800 HL	approx. kg	KERN
HK-D	D	170 – 960	1	not standard	0,45	961-131
HK-DB	D	170 – 960	1	standard	0,45	961-131