

# FO patch cable - FL MM PATCH 5,0 SC-SCRJ - 2901814

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Assembled FO cable, break out cable, multi-mode fiberglass 50/125 µm, connector: SC Duplex / B-FOC (ST), protection type: IP20, for installation in cable ducts or control cabinets, length: 5 m

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356634557

## Technical data

### Cable type

<b>Cable type</b>	Multimode fiberglass
<b>Cable, attenuation</b>	2.5 dB/km (at 850 nm), 0.7 dB/km (at 1300 nm)

### Ambient conditions

<b>Ambient temperature (operation)</b>	-5 °C ... 70 °C
<b>Ambient temperature (storage/transport)</b>	-25 °C ... 70 °C
<b>Ambient temperature (installation)</b>	-5 °C ... 50 °C
<b>Resistance to oil</b>	Not resistant to oil, gasoline, acids, and lyes

### External sheath

<b>Outer sheath, material</b>	FRNC
<b>External sheath, color</b>	orange
<b>External sheath, strain relief elements</b>	Non-metallic, aramide fiber
<b>External diameter max.</b>	5.7 mm

### Single wire

<b>Individual wires per module</b>	2
<b>Individual wire, diameter</b>	2.8 mm

### Mechanical properties

<b>Bending radius short term/long term</b>	30 mm
<b>Bending radius, long-term</b>	60 mm
<b>Lateral pressure, long-term</b>	60 N/cm
<b>Tensile strength short-term/long-term</b>	600 N

### General

<b>Cable weight</b>	15.8 kg/km
---------------------	------------

# FO patch cable - FL MM PATCH 5,0 SC-SCRJ - 2901814

## Technical data

### Behavior in fire

Flame resistance	According to DIN 60332-1-2
Flame resistance	IEC 60332-3-22 (Cat. A)
Concentration of fumes	in accordance with IEC 61034
Halogen-free	According to IEC 60754-2
Behavior in fire	No corrosive or toxic fumes
Behavior in fire	0.36 MJ/m

## classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27061003
eCl@ss 5.0	27061003
eCl@ss 5.1	27061003
eCl@ss 6.0	27259207
eCl@ss 7.0	27259207
eCl@ss 8.0	19170190

### ETIM

ETIM 2.0	EC000034
ETIM 3.0	EC000034
ETIM 4.0	EC000034
ETIM 5.0	EC000830

### UNSPSC

UNSPSC 6.01	26121607
UNSPSC 7.0901	26121607
UNSPSC 11	26121607
UNSPSC 12.01	26121607
UNSPSC 13.2	26121607

## accessories

### Adapter

PSM-SET-BFOC-LINK/2 - 2799429



## FO patch cable - FL MM PATCH 5,0 SC-SCRJ - 2901814

accessories

FL MM PATCH COUPLER LC-LC - 2700312



FL COUPLER SC-DUPLEX - 2901788



**Fiber optics connector (device side)**

VS-SCRJ-GOF-BU/BU - 1652978



**Data cable by the meter**

PSM-LWL-GDM-RUGGED- 50/125 - 2799322



PSM-LWL-GDO- 50/125 - 2799432



**Data cable preassembled**

## FO patch cable - FL MM PATCH 5,0 SC-SCRJ - 2901814

### accessories

FOC-GDM-RUGGED-1016/IP20/... - 2901558



FOC-GDM-RUGGED-1016/... - 1402193



FOC-GDO-1017/IP20/... - 2901559



### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>