




Discover more details and matching accessories online!

Lever operated test stand for hardness testing with base plate made of glass

Features

- For Shore hardness testing of plastics, leather etc.
- **1** Glass plate: high measurement accuracy by means of superior hardness of the glass plate
- **2** Mechanical construction: Robust design enables accurate measuring movements
- **3** Level adjustment: For the precise levelling of the base plate, e.g. for the correction of inhomogeneous test objects
- **4** SAUTER TI-DL: with exchangeable longer column for use with digital hardness tester HD
- Hardness tester is not included with delivery

- Operation:
 1. The SAUTER hardness testing device HB/HD is fitted in a suspended position
 2. The test object is placed on the round testing table right under the durometer measuring tip
 3. By pressing the lever down, the test weight will be released, and this then presses the measuring tip into the test object with its own weight (see test force hardness measurement)
- The accuracy of the displayed result is about 25 % higher than in a manual operated test

Technical data

- Stroke length: 15 mm
- Base plate $\varnothing$ 75 mm



Model	Hardness scales	Test force hardness measurement	Test object height [Max] mm	Overall dimensions W×D×H mm	Net weight approx. kg
SAUTER		N			
TI-AC	Shore A	10	60	150×200×330	7
TI-D	Shore D	50	60	150×200×400	8
TI-ACL	Shore A	10	290	150×200×580	6
TI-DL	Shore D	50	290	150×200×580	9