

Cable - CABLE-D25SUB/B/2X14/300/TU812 - 2304665

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Splitting cable for ABB S800 I/O, cable length 3 m

Key commercial data

package_quantity	1
GTIN	4017918951344

Technical data

General

Nominal voltage U_N	< 50 V AC
Nominal voltage U_N	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m
Length of cable	3 m
Single wire, cross section	0.14 mm ²
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	6.3 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Connector, module side

Number of positions	14
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	2

Connector, controller side

Number of positions	25
Connectors	D-SUB socket strip
Number of plugs	1

Cable - CABLE-D25SUB/B/2X14/300/TU812 - 2304665

Technical data

Supported controller

Control	ABB S800 I/O
- suitable I/O card	DI810
- suitable I/O card	DI811
- suitable I/O card	DI814
- suitable I/O card	DI830
- suitable I/O card	DI831
- suitable I/O card	DI840
- suitable I/O card	DI885
- suitable I/O card	DO810
- suitable I/O card	DO814
- suitable I/O card	DO840

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000830

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Drawings