

Interface module - FLKMS 50 - 2281597

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 50-pos.



Key commercial data

| | |
|------------------|---------------|
| package_quantity | 5 |
| GTIN | 4017918054847 |

Technical data

Dimensions

| | |
|--------|----------|
| Width | 101.5 mm |
| Height | 77 mm |
| Depth | 72 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

General

| | |
|---|-----------------------|
| Nominal voltage U_N | < 50 V AC |
| Nominal voltage U_N | 60 V DC |
| Max. current carrying capacity per branch | 1 A |
| Number of positions | 50 |
| Test voltage | 500 V (50 Hz, 1 min.) |
| Mounting position | Any |
| Standards/regulations | IEC 60664 |
| Standards/regulations | DIN EN 50178 |
| Standards/regulations | IEC 62103 |

Connection data for connection 1

| | |
|------------------------------------|---------------------|
| Connection name | PCB connection |
| Connection in acc. with standard | IEC / EN |
| Connection method | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |

Interface module - FLKMS 50 - 2281597

Technical data

Connection data for connection 1

| | |
|--|---------------------|
| Conductor cross section solid max. | 4 mm ² |
| Conductor cross section stranded min. | 0.2 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 24 |
| Conductor cross section AWG/kcmil max | 12 |
| Stripping length | 8 mm |
| Screw thread | M3 |

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250313 |
| eCl@ss 4.1 | 27250313 |
| eCl@ss 5.0 | 27250313 |
| eCl@ss 5.1 | 27250313 |
| eCl@ss 6.0 | 27242608 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001434 |
| ETIM 3.0 | EC001604 |
| ETIM 4.0 | EC001604 |
| ETIM 5.0 | EC002780 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211824 |
| UNSPSC 7.0901 | 39121421 |
| UNSPSC 11 | 39121421 |
| UNSPSC 12.01 | 39121421 |
| UNSPSC 13.2 | 39121421 |

approvals

GOST /

Approval details

| |
|--|
| GOST  |
|--|

Interface module - FLKMS 50 - 2281597

accessories

System cable

FLK 50/EZ-DR/ 50/KONFEK - 2289065



FLK 50/EZ-DR/ 100/KONFEK - 2289078



FLK 50/EZ-DR/ 150/KONFEK - 2289081



FLK 50/EZ-DR/ 200/KONFEK - 2289094



FLK 50/EZ-DR/ 250/KONFEK - 2289104



Interface module - FLKMS 50 - 2281597

accessories

FLK 50/EZ-DR/ 300/KONFEK - 2289117



FLK 50/EZ-DR/ 350/KONFEK - 2289120



FLK 50/EZ-DR/ 400/KONFEK - 2289133



FLK 50/EZ-DR/ 450/KONFEK - 2289573



FLK 50/EZ-DR/ 500/KONFEK - 2289586



FLK 50/EZ-DR/ 550/KONFEK - 2289599



Interface module - FLKMS 50 - 2281597

accessories

FLK 50/EZ-DR/ 600/KONFEK - 2289609



FLK 50/EZ-DR/ 650/KONFEK - 2289612



FLK 50/EZ-DR/ 700/KONFEK - 2289625



FLK 50/EZ-DR/ 750/KONFEK - 2289638



FLK 50/EZ-DR/ 800/KONFEK - 2289641



Interface module - FLKMS 50 - 2281597

accessories

FLK 50/EZ-DR/ 850/KONFEK - 2289654



FLK 50/EZ-DR/ 900/KONFEK - 2289667



FLK 50/EZ-DR/ 950/KONFEK - 2289670



FLK 50/EZ-DR/1000/KONFEK - 2289683



FLK EZ-DR.../.../... - 2295059



FLK 50/EZ-DR/ 50/KONFEK/S - 2299097



Interface module - FLKMS 50 - 2281597

accessories

FLK 50/EZ-DR/ 100/KONFEK/S - 2299107



FLK 50/EZ-DR/ 150/KONFEK/S - 2299110



FLK 50/EZ-DR/ 200/KONFEK/S - 2299123



FLK 50/EZ-DR/ 300/KONFEK/S - 2299136



FLK 50/EZ-DR/ 400/KONFEK/S - 2299149



Interface module - FLKMS 50 - 2281597

accessories

FLK 50/EZ-DR/ 600/KONFEK/S - 2299152



FLK 50/EZ-DR/ 800/KONFEK/S - 2299165



FLK 50/EZ-DR/1000/KONFEK/S - 2299178



FLK EZ-DR-S.../.../... - 2295046



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>