

# Interface module - VIP-3/SC/D25SUB/F - 2315188

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and female D-Subminiature pin strip, for mounting on NS 35 rails, 25-pos.

The illustration shows version VIP-3/SC/D50SUB/M

## Product Features

- 9 to 50-pos.
- Metal foot
- According to IEC 60603-13
- 1:1 connection
- Screw connection



## Key commercial data

package_quantity	1
GTIN	4046356313346

## Technical data

### Dimensions

Width	57.4 mm
Height	69 mm
Depth	62 mm

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

### General

Nominal voltage $U_N$	125 V AC/DC
Max. current carrying capacity per branch	2 A
Number of positions	25
Status display	No
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178

# Interface module - VIP-3/SC/D25SUB/F - 2315188

## Technical data

### General

<b>Standards/regulations</b>	IEC 62103
<b>Pollution degree</b>	2
<b>Surge voltage category</b>	II
<b>Rated surge voltage</b>	1.2 kV

### Connection data for connection 1

<b>Connection name</b>	PCB connection
<b>Connection in acc. with standard</b>	IEC / EN
<b>Connection method</b>	Screw connection
<b>Conductor cross section solid min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	4 mm <sup>2</sup>
<b>Conductor cross section stranded min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	24
<b>Conductor cross section AWG/kcmil max</b>	12
<b>Stripping length</b>	8 mm
<b>Screw thread</b>	M 3

### Connection data for connection 2

<b>Connection name</b>	D-SUB connection
<b>Number of connections</b>	1
<b>Connection method</b>	D-SUB socket strip
<b>Number of positions</b>	25

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27250313
<b>eCl@ss 4.1</b>	27250313
<b>eCl@ss 5.0</b>	27250313
<b>eCl@ss 5.1</b>	27250313
<b>eCl@ss 6.0</b>	27242608
<b>eCl@ss 7.0</b>	27242608
<b>eCl@ss 8.0</b>	27242608

### ETIM

<b>ETIM 2.0</b>	EC001434
<b>ETIM 3.0</b>	EC001604
<b>ETIM 4.0</b>	EC001604
<b>ETIM 5.0</b>	EC001604

### UNSPSC

<b>UNSPSC 6.01</b>	30211824
<b>UNSPSC 7.0901</b>	39121421

# Interface module - VIP-3/SC/D25SUB/F - 2315188

## classifications

### UNSPSC

<b>UNSPSC 11</b>	39121421
<b>UNSPSC 12.01</b>	39121421
<b>UNSPSC 13.2</b>	39121421

## approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized /

### Approval details

<b>CSA</b>	
Nominal voltage UN	105 V
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	30-12

<b>UL Recognized</b>	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	30-12

<b>cUL Recognized</b>	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	30-12

<b>cULus Recognized</b>	
-------------------------	--

## accessories

### System cable

## Interface module - VIP-3/SC/D25SUB/F - 2315188

### accessories

CABLE-D25SUB/B/S/ 50/KONFEK/S - 2302120



CABLE-D25SUB/B/S/100/KONFEK/S - 2302133



CABLE-D25SUB/B/S/150/KONFEK/S - 2302146



CABLE-D25SUB/B/S/200/KONFEK/S - 2302159



CABLE-D25SUB/B/S/300/KONFEK/S - 2302162



CABLE-D25SUB/B/S/400/KONFEK/S - 2302175



## Interface module - VIP-3/SC/D25SUB/F - 2315188

### accessories

---

CABLE-D25SUB/B/S/600/KONFEK/S - 2302188



CABLE D-SUB-S/.../.../... - 2302340



CABLE-D25SUB/S/S/100/KONFEK/S - 2305635



CABLE-D25SUB/S/S/200/KONFEK/S - 2305648



CABLE-D25SUB/S/S/300/KONFEK/S - 2305651



## Interface module - VIP-3/SC/D25SUB/F - 2315188

### accessories

CABLE D-SUB-S-S-S/.../.../... - 2302434



CABLE D-SUB-B-B-S/.../.../... - 2302421



### Terminal marking

UC-TM 4 - 0818111



UC-TM 6 - 0818085



ZB 5,08:UNBEDRUCKT - 0809793



# Interface module - VIP-3/SC/D25SUB/F - 2315188

accessories

ZB 22:UNBEDRUCKT - 0811862



accessories

BLUEMARK X1 - 5147777



## Drawings

Circuit diagram

