

Passive module - VIP-2/SC/FLK50/PLC - 2315227

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE interface module for 32 channels

Product Features

- ☒ Can be used for digital I/O modules
- ☒ With LED as an option
- ☒ Byte-by-byte labeling



Key commercial data

package_quantity	1
GTIN	4046356313353

Technical data

Dimensions

Width	106.1 mm
Height	65.5 mm
Depth	56 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	60 V AC/DC
Max. current carrying capacity per branch	1 A
Max. total current of voltage supply	2 A (per byte)
Number of positions	50
Status display	No
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2

Passive module - VIP-2/SC/FLK50/PLC - 2315227

Technical data

General

Surge voltage category	II
Rated surge voltage	0.6 kV

Connection data for connection 1

Connection name	Field level
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M 3

Connection data for connection 2

Connection name	Control system level
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	50

Supported controller

Control	ALLEN-BRADLEY ControlLogix
- suitable I/O card	1756-IA16I
- suitable I/O card	1756-IB16D
- suitable I/O card	1756-IB16I
- suitable I/O card	1756-IB32
- suitable I/O card	1756-IH16I
- suitable I/O card	1756-OB32
- suitable I/O card	1756-IF8
- suitable I/O card	1756-IF16
- suitable I/O card	1756-HSC
- suitable I/O card	1756-M02AE
- suitable I/O card	1756-IF8H
Control	ALLEN-BRADLEY PLC 5
- suitable I/O card	1771 IBN
- suitable I/O card	1771 OBN
Control	GE-FANUC RX3i
- suitable I/O card	IC694MDL754
- suitable I/O card	IC694MDL660
Control	HONEYWELL PlantScape
- suitable I/O card	TC-IDD 321

Passive module - VIP-2/SC/FLK50/PLC - 2315227

Technical data

Supported controller

- suitable I/O card	TC-ODD 321
Control	mitsubishi MELSEC Q
- suitable I/O card	QX41
- suitable I/O card	QX41-S1
- suitable I/O card	QX42
- suitable I/O card	QX42-S1
- suitable I/O card	QX71
- suitable I/O card	QX72
- suitable I/O card	QY41P
- suitable I/O card	QY42P
- suitable I/O card	QY71
- suitable I/O card	QH42P
- suitable I/O card	QX82
- suitable I/O card	QX82-S1
Control	mitsubishi MELSEC L
- suitable I/O card	LX41C4
- suitable I/O card	LX42C4
- suitable I/O card	LY41NT1P
- suitable I/O card	LY42NT1P
- suitable I/O card	LY41PT1P
- suitable I/O card	LY42PT1P

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC001604

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421

Passive module - VIP-2/SC/FLK50/PLC - 2315227

classifications

UNSPSC

UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

CSA / UL Recognized / cUL Recognized / UL Recognized / cULus Recognized /

Approval details

CSA 	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm²/AWG/kcmil	30-12

UL Recognized 	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm²/AWG/kcmil	30-12

cUL Recognized 	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm²/AWG/kcmil	30-12

	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm²/AWG/kcmil	30-12

Passive module - VIP-2/SC/FLK50/PLC - 2315227

approvals

cULus Recognized  US

accessories

System cable

FLK 50/EZ-DR/ 50/KONFEK - 2289065



FLK 50/EZ-DR/ 100/KONFEK - 2289078



FLK 50/EZ-DR/ 150/KONFEK - 2289081



FLK 50/EZ-DR/ 200/KONFEK - 2289094



FLK 50/EZ-DR/ 250/KONFEK - 2289104



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

FLK 50/EZ-DR/ 300/KONFEK - 2289117



FLK 50/EZ-DR/ 350/KONFEK - 2289120



FLK 50/EZ-DR/ 400/KONFEK - 2289133



FLK 50/EZ-DR/ 450/KONFEK - 2289573



FLK 50/EZ-DR/ 500/KONFEK - 2289586



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

FLK 50/EZ-DR/ 550/KONFEK - 2289599



FLK 50/EZ-DR/ 600/KONFEK - 2289609



FLK 50/EZ-DR/ 650/KONFEK - 2289612



FLK 50/EZ-DR/ 700/KONFEK - 2289625



FLK 50/EZ-DR/ 750/KONFEK - 2289638



FLK 50/EZ-DR/ 800/KONFEK - 2289641



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

FLK 50/EZ-DR/ 850/KONFEK - 2289654



FLK 50/EZ-DR/ 900/KONFEK - 2289667



FLK 50/EZ-DR/ 950/KONFEK - 2289670



FLK 50/EZ-DR/1000/KONFEK - 2289683



FLK EZ-DR.../.../... - 2295059



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

FLK 50/EZ-DR/ 50/KONFEK/S - 2299097



FLK 50/EZ-DR/ 100/KONFEK/S - 2299107



FLK 50/EZ-DR/ 150/KONFEK/S - 2299110



FLK 50/EZ-DR/ 200/KONFEK/S - 2299123



FLK 50/EZ-DR/ 300/KONFEK/S - 2299136



FLK 50/EZ-DR/ 400/KONFEK/S - 2299149



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

FLK 50/EZ-DR/ 600/KONFEK/S - 2299152



FLK 50/EZ-DR/ 800/KONFEK/S - 2299165



FLK 50/EZ-DR/1000/KONFEK/S - 2299178



FLK EZ-DR-S.../.../... - 2295046



CABLE-FLK50/0,14/HF/ 0,5M - 2314134



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

CABLE-FLK50/0,14/HF/ 1,0M - 2314147



CABLE-FLK50/0,14/HF/ 1,5M - 2314150



CABLE-FLK50/0,14/HF/ 2,0M - 2314163



CABLE-FLK50/0,14/HF/ 2,5M - 2314176



CABLE-FLK50/0,14/HF/ 5,0M - 2314202



CABLE-FLK50/0,14/HF/ 6,0M - 2314215



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

CABLE-FLK50/0,14/HF/ 7,0M - 2314228



CABLE-FLK50/0,14/HF/ 8,0M - 2314231



CABLE-FLK50-0,14-HF/... - 2314257



Terminal marking

UC-TM 4 - 0818111



UC-TM 6 - 0818085



Passive module - VIP-2/SC/FLK50/PLC - 2315227

accessories

ZB 5,08:UNBEDRUCKT - 0809793



ZB 22:UNBEDRUCKT - 0811862




accessories

BLUEMARK X1 - 5147777



Drawings

Circuit diagram



VIP-2/SC/FLK50/PLC connection scheme

