

Solenoid driver - MACX MCR-EX-SL-SD-21-40-LP - 2865764

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ex-i solenoid driver. For controlling Ex-i solenoid valves, alarm modules or LEDs installed in Ex areas. Current limitation at 40 mA. For gases up to Group II C, loop-powered, electrical isolation, SIL 3.

Product Features

- Mechanically compatible with the DIN rail connector
- Various output characteristic curves compatible with standard solenoid valves
- Loop-powered: the required power is supplied via the control signal on the input side.
- Up to SIL 3 according to EN 61508
- Installation in zone 2, protection type "n" (EN 60079-15) permitted
- Output [Ex ia] IIC/[Ex ia] IIB
- 2-way electrical isolation
- 20
30 V DC input



Key commercial data

package_quantity	1
GTIN	4046356325233

Technical data

Dimensions

Width	12.5 mm
Height	99 mm
Depth	114.5 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (Any mounting position)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Maximum altitude	≤ 2000 m
Permissible humidity (operation)	10 % ... 95 % (no condensation)
Degree of protection	IP20

Output data

Output characteristic curve: Output resistor	287 Ω (Internal resistance R _i)
--	---

Solenoid driver - MACX MCR-EX-SL-SD-21-40-LP - 2865764

Technical data

Output data

Response time	20 ms
----------------------	-------

Compatible valves

Note	This is an extract of possible combinations of valves and solenoid drivers.
Compatible valve	ASCO Coil 195
Compatible valve	Bürkert Coil AC 10 standard
Compatible valve	Bürkert Coil AC 10 high resistance
Compatible valve	Bürkert Coil AC 21 standard 700 mW / 65°C
Compatible valve	Bürkert Coil AC 21 high resistance 700 mW / 65°C
Compatible valve	Bürkert Coil AC 21 standard 900 mW / 45°C
Compatible valve	Bürkert Coil AC 21 high resistance 900 mW / 45°C
Compatible valve	Bürkert Coil AC 21 standard 900 mW / 60°C
Compatible valve	Bürkert Coil AC 21 high resistance 900 mW / 60°C
Compatible valve	Bürkert Coil G1 642735 standard 600 mW / 50°C
Compatible valve	Bürkert Coil G1 642735 high resistance 600 mW / 50°C
Compatible valve	Bürkert Coil G1 642735 standard 800 mW / 40°C
Compatible valve	Bürkert Coil G1 642735 high resistance 800 mW / 40°C
Compatible valve	Bürkert Coil G1 642735 standard 1000 mW / 40°C
Compatible valve	Bürkert Coil G1 642735 high resistance 1000 mW / 40°C
Compatible valve	Norgren Herion Coil 2050
Compatible valve	Norgren Herion Coil 2051
Compatible valve	Norgren Herion Coil 2052
Compatible valve	Norgren Herion Coil 2080 / 2082
Compatible valve	Norgren Herion Coil 2081 / 2083
Compatible valve	Norgren Herion Coil 2084
Compatible valve	Hörbiger Piezo P8 38x RF-Nx-SPN65 30 V type
Compatible valve	Hörbiger Piezo P20 381RF-NG-CPN61 30 V type
Compatible valve	Parker Coil VZ07 488650.01
Compatible valve	Parker Coil VZ33 494035.10
Compatible valve	Parker Coil VZ08 488660.01
Compatible valve	Parker Coil VZ09 488670.01
Compatible valve	Parker Coil VZ95 482160.01 EEEx ia IIB T6
Compatible valve	Parker Coil VZ23 482870.01
Compatible valve	Samson Coil 3701-12 (12 V)
Compatible valve	Samson Coil 3701-13 (24 V)
Compatible valve	Samson Coil 3963-12 (12 V)
Compatible valve	Samson Coil 3963-13 (24 V)
Compatible valve	Samson Coil 3964-12 (12 V)
Compatible valve	Samson Coil 3964-13 (24 V)
Compatible valve	Seitz Pilot valve PV 12F73 Ci oH
Compatible valve	Seitz Pilot valve PV 12F73 Xi oH

Solenoid driver - MACX MCR-EX-SL-SD-21-40-LP - 2865764

Technical data

Compatible valves

Compatible valve	Seitz Pilot valve PV 12F73 Xi oH-2
------------------	------------------------------------

Power supply

Power consumption	< 1.2 W
-------------------	---------

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Stripping length	7 mm
Screw thread	M3
Connection method	Screw connection
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

General

No. of channels	1
Maximum temperature coefficient	0.01 %/K
Status display	Yellow LED (switching state / status, lights up when output circuit is active)
Inflammability class according to UL 94	V0
Pollution degree	2
Surge voltage category	II
Housing material	PA 66-FR
Color	green
Name	Output/input
Electrical isolation	375 V (Peak value in accordance with EN 60079-11)
Electrical isolation	300 V _{rms} (Rated insulation voltage (surge voltage category II; pollution degree 2, safe isolation as per EN 61010-1))
Electrical isolation	2.5 kV (50 Hz, 1 min., test voltage)
Conformance	CE-compliant, additionally EN 61326
ATEX	# II 3 G Ex nA IIC T4 Gc X
ATEX	# II (1) G [Ex ia Ga] IIC/IIB/IIA
ATEX	# II (1) D [Ex ia Da] IIIC
IECEX	[Ex ia Ga] IIC/IIB/IIA
IECEX	[Ex ia Da] IIIC
IECEX	Ex nA IIC T4 Gc X
UL, USA / Canada	Class I Div 2; IS for Class I, II, III Div 1
Functional safety (SIL)	SIL 3

Safety characteristic data

Solenoid driver - MACX MCR-EX-SL-SD-21-40-LP - 2865764

Technical data

Safety characteristic data

Integrity requirement	IEC 61508 - Low demand
Equipment type	Type A
Safety Integrity Level (SIL)	3
Safe Failure Fraction (SFF)	100 %
λ_{SU}	2.84×10^{-7} (284 FIT)
λ_{SD}	0
λ_{DU}	0
λ_{DD}	0
Probability of a hazardous failure on demand (PFD _{AVG})	0 (1 year)
Probability of a hazardous failure on demand (PFD _{AVG})	0 (5 years)
Probability of a hazardous failure on demand (PFD _{AVG})	0 (10 years)
Diagnostic coverage (DC)	(DC _S = 0%, DC _D = 0%)

Safety data

Input power P _i	(negligible)
Max. internal capacitance C _i	(negligible)
Max. output voltage U _o	25.1 V
Max. output current I _o	87 mA
Max. output power P _o	550 mW
Gas group	IIC
Max. external inductivity L _o	6.3 mH
Max. external capacity C _o	0.1 µF
Gas group	IIB
Max. external inductivity L _o	26 mH
Max. external capacity C _o	0.8 µF
Gas group	IIA
Max. external inductivity L _o	56 mH
Max. external capacity C _o	2.9 µF
Safety-related maximum voltage U _m	253 V AC (125 V DC)

classifications

eCl@ss

eCl@ss 4.0	27210121
eCl@ss 4.1	27210121
eCl@ss 5.0	27210121
eCl@ss 5.1	27210121
eCl@ss 6.0	27210121
eCl@ss 7.0	27210121
eCl@ss 8.0	27210121

ETIM

Solenoid driver - MACX MCR-EX-SL-SD-21-40-LP - 2865764

classifications

ETIM

ETIM 2.0	EC001430
ETIM 3.0	EC001599
ETIM 4.0	EC001599
ETIM 5.0	EC001599

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	39121008

approvals

IECEX / UL Listed / cUL Listed / ATEX / IECEx / ATEX / cULus Listed / UL Listed / cUL Listed / Functional Safety / cULus Listed /

Approval details

IECEX

UL Listed

cUL Listed

ATEX

cULus Listed

Solenoid driver - MACX MCR-EX-SL-SD-21-40-LP - 2865764

approvals




Functional Safety




Drawings

Block diagram



Solenoid driver - MACX MCR-EX-SL-SD-21-40-LP - 2865764

Diagram



Dimensioned drawing

