

D-SUB coaxial contact - VS-BU-KX-50-RG58 - 1655577

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Coaxial contact, for D-SUB combination inserts, solder cup, socket, straight, for cable RG 58, gold-plated

Key commercial data

package_quantity	10
GTIN	4046356029483

Technical data

Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
Connection method	Solder cup
Conductor cross section	0.8 mm ²
Connection cross section AWG	18
External cable diameter	5.2 mm
Insertion force per signal contact	≤ 7.00 N
Extraction force per signal contact	≤ 7 N

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
--	-------------------

Material data

Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel

Electrical characteristics

Rated voltage (III/3)	250 V
Rated current	2 A
Insulation resistance	10 TΩ

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701

D-SUB coaxial contact - VS-BU-KX-50-RG58 - 1655577

classifications

eCl@ss

eCl@ss 6.0	27261202
eCl@ss 7.0	27440204
eCl@ss 8.0	27440204

ETIM

ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

accessories

Assembly tool


HC-M4-KOAX-EWZ - 1676747



Drawings

D-SUB coaxial contact - VS-BU-KX-50-RG58 - 1655577

Dimensioned drawing



D-SUB coaxial contact socket

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>