

Interface module - VIP-3/SC/FLK26 - 2315052

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 26-pos.

Product Features

- 10 to 64-pos.
- Metal foot
- According to IEC 60603-13
- 1:1 connection
- Screw connection



Key commercial data

package_quantity	1
GTIN	4046356312882

Technical data

Dimensions

Width	57.1 mm
Height	69 mm
Depth	62 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	60 V AC/DC
Max. current carrying capacity per branch	1 A
Number of positions	26
Status display	No
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103

Interface module - VIP-3/SC/FLK26 - 2315052

Technical data

General

Pollution degree	2
Surge voltage category	II
Rated surge voltage	0.6 kV

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M 3

Connection data for connection 2

Connection name	Control system level
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	26

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC001604

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421

Interface module - VIP-3/SC/FLK26 - 2315052

classifications

UNSPSC

UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

CSA / cUL Recognized /

Approval details

CSA	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm ² /AWG/kcmil	30-12

cUL Recognized	
Nominal voltage UN	125 V
Nominal current IN	1 A
mm ² /AWG/kcmil	30-12

accessories

System cable

VIP-CAB-FLK26/0,14/0,5M - 2318622



VIP-CAB-FLK26/0,14/1,0M - 2318635



Interface module - VIP-3/SC/FLK26 - 2315052

accessories

VIP-CAB-FLK26/0,14/1,5M - 2318648



VIP-CAB-FLK26/0,14/2,0M - 2318651



VIP-CAB-FLK26/0,14/3,0M - 2318664



VIP-CAB-FLK26/0,14/4,0M - 2318677



VIP-CAB-FLK26/0,14/6,0M - 2318680



Interface module - VIP-3/SC/FLK26 - 2315052

accessories

VIP-CAB-FLK26-0,14/... - 2318693



FLK 26/EZ-DR/ 50/KONFEK - 2299385



FLK 26/EZ-DR/ 100/KONFEK - 2299398



FLK 26/EZ-DR/ 150/KONFEK - 2299408



FLK 26/EZ-DR/ 200/KONFEK - 2299411



FLK 26/EZ-DR/ 300/KONFEK - 2299424



Interface module - VIP-3/SC/FLK26 - 2315052

accessories

FLK 26/EZ-DR/ 400/KONFEK - 2299437



FLK 26/EZ-DR/ 600/KONFEK - 2299440



FLK 26/EZ-DR/ 800/KONFEK - 2299453



FLK 26/EZ-DR/1000/KONFEK - 2299466



FLK EZ-DR.../.../... - 2295059



Terminal marking

Interface module - VIP-3/SC/FLK26 - 2315052

accessories

UC-TM 4 - 0818111



UC-TM 6 - 0818085



ZB 5,08:UNBEDRUCKT - 0809793



ZB 22:UNBEDRUCKT - 0811862



accessories


BLUEMARK X1 - 5147777



Drawings

Interface module - VIP-3/SC/FLK26 - 2315052

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>