

Interface module - UM 25-D15SUB/B/FRONT/Q - 2959586

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE SLIM LINE, with screw connection and D-subminiature socket strip, for assembly at a right angle on NS 35/7.5, 15 positions

The illustration shows the version UM 25-D 9SUB/B/FRONT/Q



Key commercial data

| | |
|------------------|---------------|
| package_quantity | 1 |
| GTIN | 4017918086237 |

Technical data

Dimensions

| | |
|--------|--------|
| Width | 25 mm |
| Height | 147 mm |
| Depth | 45 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -10 °C ... 50 °C |
| Ambient temperature (storage/transport) | -10 °C ... 70 °C |

General

| | |
|---|--|
| Nominal voltage U_N | 125 V AC/DC |
| Max. current carrying capacity per branch | 2.5 A |
| Max. current carrying capacity per branch | 1.5 A (with even load on all branches) |
| Number of positions | 15 |
| Test voltage | 800 V (50 Hz, 1 min.) |
| Mounting position | Any |
| Standards/regulations | IEC 60664 |
| Standards/regulations | IEC 60664 A |
| Standards/regulations | DIN VDE 0110 |
| Standards/regulations | DIN VDE 0160 (in parts) |
| Pollution degree | 2 |
| Surge voltage category | II |
| Rated surge voltage | 1.2 kV |

Interface module - UM 25-D15SUB/B/FRONT/Q - 2959586

Technical data

General

| | |
|---------------------------------|-------|
| Rated insulation voltage | 125 V |
|---------------------------------|-------|

Connection data for connection 1

| | |
|---|---------------------|
| Connection name | PCB connection |
| Connection in acc. with standard | IEC / EN |
| Connection method | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 4 mm ² |
| Conductor cross section stranded min. | 0.2 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Conductor cross section AWG/kcmil min. | 24 |
| Conductor cross section AWG/kcmil max | 12 |
| Stripping length | 8 mm |
| Screw thread | M3 |

Connection data for connection 2

| | |
|------------------------------|--------------------|
| Connection name | D-SUB connection |
| Number of connections | 1 |
| Connection method | D-SUB socket strip |
| Number of positions | 15 |

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 27250313 |
| eCl@ss 4.1 | 27250313 |
| eCl@ss 5.0 | 27250313 |
| eCl@ss 5.1 | 27250313 |
| eCl@ss 6.0 | 27242608 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |

ETIM

| | |
|-----------------|----------|
| ETIM 2.0 | EC001434 |
| ETIM 3.0 | EC001604 |
| ETIM 4.0 | EC001604 |
| ETIM 5.0 | EC002780 |

UNSPSC

| | |
|----------------------|----------|
| UNSPSC 6.01 | 30211824 |
| UNSPSC 7.0901 | 39121421 |
| UNSPSC 11 | 39121421 |
| UNSPSC 12.01 | 39121421 |
| UNSPSC 13.2 | 39121421 |

Interface module - UM 25-D15SUB/B/FRONT/Q - 2959586

approvals

GOST /

Approval details



accessories

System cable

CABLE-D15SUB/B/S/ 50/KONFEK/S - 2302052



CABLE-D15SUB/B/S/100/KONFEK/S - 2302065



CABLE-D15SUB/B/S/150/KONFEK/S - 2302078



CABLE-D15SUB/B/S/200/KONFEK/S - 2302081



Interface module - UM 25-D15SUB/B/FRONT/Q - 2959586

accessories

CABLE-D15SUB/B/S/300/KONFEK/S - 2302094



CABLE-D15SUB/B/S/400/KONFEK/S - 2302104



CABLE-D15SUB/B/S/600/KONFEK/S - 2302117



CABLE D-SUB-S/.../.../... - 2302340



CABLE D-SUB-S-S-S/.../.../... - 2302434



CABLE-D-15SUB/M/OE/0,25/S/0,5M - 2926438



Interface module - UM 25-D15SUB/B/FRONT/Q - 2959586

accessories

CABLE-D-15SUB/M/OE/0,25/S/1,0M - 2926441



CABLE-D-15SUB/M/OE/0,25/S/1,5M - 2926454



CABLE-D-15SUB/M/OE/0,25/S/2,0M - 2926467



CABLE-D-15SUB/M/OE/0,25/S/3,0M - 2926470



CABLE-D-15SUB/M/OE/0,25/S/4,0M - 2926483



Interface module - UM 25-D15SUB/B/FRONT/Q - 2959586

accessories

CABLE-D-15SUB/M/OE/0,25/S/6,0M - 2926496



CABLE-D-15SUB-M-OE-0,25-S/... - 2900910



Drawings

Circuit diagram

