

Interface module - FLKM-D 9 SUB/B/ZFKDS - 2304034

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Standard 1:1 D-SUB module, with spring-cage connection and D-SUB socket strip, no. of positions 9

The illustration shows the version FLKM-D37 SUB/S/ZFKDS

Product Features

- 9 to 50-pos.
- Spring-cage connection technology
- According to IEC 60807-2
- 1:1 connection



Key commercial data

package_quantity	1
GTIN	4017918944001

Technical data

Dimensions

Width	33.8 mm
Height	77 mm
Depth	52 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per branch	2.5 A
Max. current carrying capacity per branch	1.5 A (with even load on all branches)
Number of positions	9
Status display	No
Test voltage	800 V (50 Hz, 1 min.)
Mounting position	Any
Assembly instructions	In rows with zero spacing

Interface module - FLKM-D 9 SUB/B/ZFKDS - 2304034

Technical data

General

Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2
Surge voltage category	II
Rated surge voltage	1.2 kV
Rated insulation voltage	125 V

Connection data for connection 1

Connection name	PCB connection
Connection method	Spring-cage connection
Number of positions	10
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	7 mm

Connection data for connection 2

Connection name	D-SUB connection
Connection method	D-SUB socket strip
Number of positions	9

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
-------------	----------

Interface module - FLKM-D 9 SUB/B/ZFKDS - 2304034

classifications


UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details



accessories

System cable

CABLE-D 9SUB/B/S/ 50/KONFEK/S - 2299987



CABLE-D 9SUB/B/S/100/KONFEK/S - 2299990



Interface module - FLKM-D 9 SUB/B/ZFKDS - 2304034

accessories

CABLE-D 9SUB/B/S/150/KONFEK/S - 2300009



CABLE-D 9SUB/B/S/200/KONFEK/S - 2302010



CABLE-D 9SUB/B/S/300/KONFEK/S - 2302023



CABLE-D 9SUB/B/S/400/KONFEK/S - 2302036



CABLE-D 9SUB/B/S/600/KONFEK/S - 2302049



CABLE D-SUB-S/.../.../... - 2302340



Interface module - FLKM-D 9 SUB/B/ZFKDS - 2304034

accessories

CABLE D-SUB-S-S/.../.../... - 2302434



CABLE-D- 9SUB/M/OE/0,25/S/0,5M - 2926360



CABLE-D- 9SUB/M/OE/0,25/S/1,0M - 2926373



CABLE-D- 9SUB/M/OE/0,25/S/1,5M - 2926386



CABLE-D- 9SUB/M/OE/0,25/S/2,0M - 2926399



Interface module - FLKM-D 9 SUB/B/ZFKDS - 2304034

accessories

CABLE-D- 9SUB/M/OE/0,25/S/3,0M - 2926409



CABLE-D- 9SUB/M/OE/0,25/S/4,0M - 2926412



CABLE-D- 9SUB/M/OE/0,25/S/6,0M - 2926425




CABLE-D- 9SUB-M-OE-0,25-S/... - 2900909



Drawings

Interface module - FLKM-D 9 SUB/B/ZFKDS - 2304034

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>