

Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 1)

- P271 Use only outdoors or in a well-ventilated area.
 P280 Wear protective gloves / eye protection / face protection.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
 P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

Additional information:

EUH066 Repeated exposure may cause skin dryness or cracking.
 Warning! Hazardous respirable droplets may be formed when sprayed. Do not breathe spray or mist.

2.3 Other hazards
Results of PBT and vPvB assessment

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

• **Description:** Mixture of substances listed below with nonhazardous additions.

Dangerous components:

CAS: 67-64-1 EINECS: 200-662-2 Reg.nr.: 01-2119471330-49	acetone Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336, EUH066	25-50%
CAS: 74-98-6 EINECS: 200-827-9 Reg.nr.: 01-2119486944-21	Propane Flam. Gas 1A, H220; Press. Gas (Liq.), H280	5-10%
CAS: 75-28-5 EINECS: 200-857-2 Reg.nr.: 01-2119485395-27	Isobutane Flam. Gas 1A, H220; Press. Gas (Comp.), H280	5-10%
CAS: 106-97-8 EINECS: 203-448-7 Reg.nr.: 01-2119474691-32	butane Flam. Gas 1A, H220; Press. Gas (Comp.), H280	5-10%
CAS: 64742-95-6 EINECS: 265-199-0 Reg.nr.: 01-2119455851-35	Solvent naphtha (petroleum), light arom. Flam. Liq. 3, H226; Asp. Tox. 1, H304; Aquatic Chronic 2, H411; STOT SE 3, H335	5-10%
EC number: 919-857-5 Reg.nr.: 01-2119463258-33	Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics Flam. Liq. 3, H226; Asp. Tox. 1, H304; STOT SE 3, H336, EUH066	5-10%
CAS: 1330-20-7 EINECS: 215-535-7 Reg.nr.: 01-2119488216-32	xylene Flam. Liq. 3, H226; Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315	2.5-5%
CAS: 13463-67-7 EINECS: 236-675-5 Reg.nr.: 01-2119489379-17	titanium dioxide Carc. 2, H351	2.5-5%

• **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Do not induce vomiting; call for medical help immediately.

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 2)

- **4.2 Most important symptoms and effects, both acute and delayed**
Breathing difficulty
Headache
Dizziness
Dizziness
Nausea
- **4.3 Indication of any immediate medical attention and special treatment needed**
If swallowed or in case of vomiting, danger of entering the lungs.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
Fire-extinguishing powder
Carbon dioxide
Foam
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** Can form explosive gas-air mixtures.
- **5.3 Advice for firefighters**
- **Protective equipment:** Wear self-contained respiratory protective device.
- **Additional information**
Cool endangered receptacles with water spray.
Dispose of fire debris and contaminated fire fighting water in accordance with official regulations.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
Ensure adequate ventilation
Keep away from ignition sources.
- **6.2 Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
Do not spray onto a naked flame or any incandescent material.

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 3)

- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Store in a cool location.
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
Store in cool, dry conditions in well sealed receptacles.
Protect from heat and direct sunlight.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

· 8.1 Control parameters

· **Ingredients with limit values that require monitoring at the workplace:**

67-64-1 acetone (25-50%)

WEL	Short-term value: 3620 mg/m ³ , 1500 ppm Long-term value: 1210 mg/m ³ , 500 ppm
-----	--

106-97-8 butane (5-10%)

WEL	Short-term value: 1810 mg/m ³ , 750 ppm Long-term value: 1450 mg/m ³ , 600 ppm Carc (if more than 0.1% of buta-1.3-diene)
-----	---

1330-20-7 xylene (2.5-5%)

WEL	Short-term value: 441 mg/m ³ , 100 ppm Long-term value: 220 mg/m ³ , 50 ppm Sk; BMGV
-----	--

· **Ingredients with biological limit values:**

1330-20-7 xylene (2.5-5%)

BMGV	650 mmol/mol creatinine Medium: urine Sampling time: post shift Parameter: methyl hippuric acid
------	--

- **Additional information:** The lists valid during the making were used as basis.

· 8.2 Exposure controls

- **Appropriate engineering controls** No further data; see item 7.
- **Individual protection measures, such as personal protective equipment**
- **General protective and hygienic measures:**
Avoid contact with the eyes and skin.
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
- **Respiratory protection:**
In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.
Short term filter device:
Filter AX
- **Hand protection** Solvent resistant gloves
- **Material of gloves**
Butyl rubber, BR
Recommended thickness of the material: ≥ 0.7 mm

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 4)

- **Penetration time of glove material**
Value for the permeation: Level \geq 60 min
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye/face protection** Tightly sealed goggles

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

- | | |
|---|-----------------------------------|
| · Colour: | Light grey |
| · Odour: | Characteristic |
| · Odour threshold: | Not determined. |
| · Melting point/freezing point: | Undetermined. |
| · Boiling point or initial boiling point and boiling range | Not applicable, as aerosol. |
| · Flammability | Not applicable. |
| · Lower and upper explosion limit | |
| · Lower: | Not determined. |
| · Upper: | Not determined. |
| · Flash point: | -42 °C |
| · Auto-ignition temperature: | Product is not selfigniting. |
| · Decomposition temperature: | Not determined. |
| · pH | Not determined. |
| · Viscosity: | |
| · Kinematic viscosity | Not determined. |
| · Dynamic: | Not determined. |
| · Solubility | |
| · water: | Not miscible or difficult to mix. |
| · Partition coefficient n-octanol/water (log value) | Not determined. |
| · Vapour pressure: | Not determined. |
| · Density and/or relative density | |
| · Density at 20 °C: | 0.78 g/cm ³ |
| · Relative density | Not determined. |
| · Vapour density | Not determined. |

· 9.2 Other information

- **Appearance:**
- **Form:** Aerosol
- **Important information on protection of health and environment, and on safety.**
- **Explosive properties:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
- **Change in condition**
- **Evaporation rate** Not applicable.
- **Information with regard to physical hazard classes**
- **Explosives** Void
- **Flammable gases** Void
- **Aerosols**
Extremely flammable aerosol. Pressurised container: May burst if heated.
- **Oxidising gases** Void
- **Gases under pressure** Void
- **Flammable liquids** Void
- **Flammable solids** Void
- **Self-reactive substances and mixtures** Void
- **Pyrophoric liquids** Void

(Contd. on page 6)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 5)

· Pyrophoric solids	Void
· Self-heating substances and mixtures	Void
· Substances and mixtures, which emit flammable gases in contact with water	Void
· Oxidising liquids	Void
· Oxidising solids	Void
· Organic peroxides	Void
· Corrosive to metals	Void
· Desensitised explosives	Void

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

67-64-1 acetone

Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	20,000 mg/kg (rabbit)
Inhalative	LC50/4 h	76 mg/l (rat)

64742-95-6 Solvent naphtha (petroleum), light arom.

Oral	LD50	>6,800 mg/kg (rat)
Dermal	LD50	>3,400 mg/kg (rab)
Inhalative	LC50/4 h	>10.2 mg/l (rat)

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics

Oral	LD50	>5,000 mg/kg (rat)
Dermal	LD50	>5,000 mg/kg (rabbit)
Inhalative	LC50/4 h	>4,951 mg/l (rat)

1330-20-7 xylene

Oral	LD50	3,523 mg/kg (rat)
Dermal	LD50	12,126 mg/kg (rabbit)
Inhalative	LC50/4 h	27,571 mg/l (rat)

13463-67-7 titanium dioxide

Oral	LD50	>20,000 mg/kg (rat)
Dermal	LD50	>10,000 mg/kg (rabbit)
Inhalative	LC50/4 h	>6.82 mg/l (rat)

- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.

(Contd. on page 7)

Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 6)

- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1 Toxicity

Aquatic toxicity:

1330-20-7 xylene

EC50	165 mg/l (daphnia)
------	--------------------

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.
- **12.7 Other adverse effects**
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

- **14.1 UN number or ID number**
- **ADR, IMDG, IATA** UN1950
- **14.2 UN proper shipping name**
- **ADR, IMDG** AEROSOLS
- **IATA** AEROSOLS, flammable
- **14.3 Transport hazard class(es)**

ADR



- **Class** 2 5F Gases.
- **Label** 2.1

(Contd. on page 8)

Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 7)

· IMDG, IATA


<ul style="list-style-type: none"> · Class · Label · 14.4 Packing group · ADR, IMDG, IATA · 14.5 Environmental hazards: · Marine pollutant: · 14.6 Special precautions for user · Hazard identification number (Kemler code): · EMS Number: · Stowage Code 	<p>2.1 Gases. 2.1</p> <p>Void</p> <p>No Warning: Gases.</p> <p>-</p> <p>F-D,S-U SW1 Protected from sources of heat. SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters. SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.</p>
<ul style="list-style-type: none"> · Segregation Code 	<p>SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.</p>
<ul style="list-style-type: none"> · 14.7 Maritime transport in bulk according to IMO instruments 	<p>Not applicable.</p>
<ul style="list-style-type: none"> · Transport/Additional information: 	
<ul style="list-style-type: none"> · ADR · Excepted quantities (EQ): · Limited quantities (LQ) · Transport category · Tunnel restriction code · UN "Model Regulation": 	<p>E0 1L 2 D UN 1950 AEROSOLS, 2.1</p>

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
Please note TRGS 510.
- **Directive 2012/18/EU**
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.

(Contd. on page 9)

Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 26.11.2021

Version number 1

Revision: 26.11.2021

Trade name: CARAMBA Profi High performance primer (Aerosol)

(Contd. of page 8)

H312 Harmful in contact with skin.
 H315 Causes skin irritation.
 H319 Causes serious eye irritation.
 H332 Harmful if inhaled.
 H335 May cause respiratory irritation.
 H336 May cause drowsiness or dizziness.
 H351 Suspected of causing cancer.
 H411 Toxic to aquatic life with long lasting effects.
 EUH066 Repeated exposure may cause skin dryness or cracking.

Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Flam. Gas 1A: Flammable gases – Category 1A

Aerosol 1: Aerosols – Category 1

Press. Gas (Comp.): Gases under pressure – Compressed gas

Press. Gas (Liq.): Gases under pressure – Liquefied gas

Flam. Liq. 2: Flammable liquids – Category 2

Flam. Liq. 3: Flammable liquids – Category 3

Acute Tox. 4: Acute toxicity – Category 4

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

Carc. 2: Carcinogenicity – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

Asp. Tox. 1: Aspiration hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

*** Data compared to the previous version altered.**