



# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 05.09.2022

Version number 8

Revision: 05.09.2022

**Trade name: CARAMBA Profi High performance rust remover Rasant(Aerosol)**

(Contd. of page 1)

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**

CAS: 246538-78-3 Reg.nr.: 01-2119456810-40	Hydrocarbons, C11-C13, isoalkanes, < 2%aromatics Asp. Tox. 1, H304, EUH066	25-50%
CAS: 112-34-5 EINECS: 203-961-6 Reg.nr.: 01-2119475104-44	2-(2-butoxyethoxy)ethanol Eye Irrit. 2, H319	10-25%
CAS: 106-97-8 EINECS: 203-448-7 Reg.nr.: 01-2119474691-32	butane Flam. Gas 1A, H220; Press. Gas (Comp.), H280	10-25%
CAS: 111-76-2 EINECS: 203-905-0 Reg.nr.: 01-2119475108-36	2-butoxyethanol Acute Tox. 4, H302; Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319	5-10%
CAS: 74-98-6 EINECS: 200-827-9 Reg.nr.: 01-2119486944-21	Propane Flam. Gas 1A, H220; Press. Gas (Liq.), H280	2.5-5%
CAS: 124-38-9 EINECS: 204-696-9	Carbondioxide Press. Gas (Comp.), H280	1-2.5%

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

### SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**  
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed**  
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.

(Contd. on page 3)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 05.09.2022

Version number 8

Revision: 05.09.2022

Trade name: **CARAMBA Profi High performance rust remover Rasant(Aerosol)**

(Contd. of page 2)

- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

### SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:** Ensure adequate ventilation.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**  
Keep ignition sources away - Do not smoke.  
Protect against electrostatic charges.  
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.  
Do not spray onto a naked flame or any incandescent material.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Store in a cool location.  
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**  
Store in cool, dry conditions in well sealed receptacles.  
Protect from heat and direct sunlight.
- **7.3 Specific end use(s)** No further relevant information available.

### SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**

- **Ingredients with limit values that require monitoring at the workplace:**

<b>112-34-5 2-(2-butoxyethoxy)ethanol (10-25%)</b>	
WEL	Short-term value: 101.2 mg/m <sup>3</sup> , 15 ppm Long-term value: 67.5 mg/m <sup>3</sup> , 10 ppm
<b>106-97-8 butane (10-25%)</b>	
WEL	Short-term value: 1810 mg/m <sup>3</sup> , 750 ppm Long-term value: 1450 mg/m <sup>3</sup> , 600 ppm Carc (if more than 0.1% of buta-1.3-diene)
<b>34590-94-8 Dipropylene glycol monomethyl ether (10-25%)</b>	
WEL	Long-term value: 308 mg/m <sup>3</sup> , 50 ppm Sk
<b>111-76-2 2-butoxyethanol (5-10%)</b>	
WEL	Short-term value: 246 mg/m <sup>3</sup> , 50 ppm Long-term value: 123 mg/m <sup>3</sup> , 25 ppm Sk, BMGV

(Contd. on page 4)

# Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 05.09.2022

Version number 8

Revision: 05.09.2022

**Trade name: CARAMBA Profi High performance rust remover Rasant(Aerosol)**

(Contd. of page 3)

### 124-38-9 Carbondioxide (1-2.5%)

WEL Short-term value: 27400 mg/m<sup>3</sup>, 15000 ppm  
Long-term value: 9150 mg/m<sup>3</sup>, 5000 ppm

#### · **Ingredients with biological limit values:**

### 111-76-2 2-butoxyethanol (5-10%)

BMGV 240 mmol/mol creatinine  
Medium: urine  
Sampling time: post shift  
Parameter: butoxyacetic acid

· **Additional information:** The lists valid during the making were used as basis.

#### · **8.2 Exposure controls**

· **Appropriate engineering controls** No further data; see item 7.

· **Individual protection measures, such as personal protective equipment**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes.

· **Respiratory protection:** Use suitable respiratory protective device in case of insufficient ventilation.

· **Hand protection** Solvent resistant gloves

· **Material of gloves** Nitrile rubber, NBR

· **Penetration time of glove material** Value for the permeation: Level  $\geq$  480 min

· **Eye/face protection** Tightly sealed goggles

## SECTION 9: Physical and chemical properties

### · **9.1 Information on basic physical and chemical properties**

#### · **General Information**

· **Colour:**

Clear

· **Odour:**

Characteristic

· **Odour threshold:**

Not determined.

· **Melting point/freezing point:**

Undetermined.

· **Boiling point or initial boiling point and boiling range**

Not applicable, as aerosol.

· **Flammability**

Not applicable.

· **Lower and upper explosion limit**

· **Lower:**

Not determined.

· **Upper:**

Not determined.

· **Flash point:**

Not applicable, as aerosol.

· **Decomposition temperature:**

Not determined.

· **pH**

Not determined.

· **Viscosity:**

· **Kinematic viscosity**

Not determined.

· **Dynamic:**

Not determined.

· **Solubility**

· **water:**

Not miscible or difficult to mix.

· **Partition coefficient n-octanol/water (log value)**

Not determined.

· **Vapour pressure:**

Not determined.

· **Density and/or relative density**

· **Density at 20 °C:**

0.84 g/cm<sup>3</sup>

· **Relative density**

Not determined.

· **Vapour density**

Not determined.

(Contd. on page 5)

# Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 05.09.2022

Version number 8

Revision: 05.09.2022

**Trade name: CARAMBA Profi High performance rust remover Rasant(Aerosol)**

(Contd. of page 4)

- **9.2 Other information**
- **Appearance:**
- **Form:** Aerosol
- **Important information on protection of health and environment, and on safety.**
- **Auto-ignition temperature:** Product is not selfigniting.
- **Explosive properties:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
- **Change in condition**
- **Evaporation rate** Not applicable.
- **Information with regard to physical hazard classes**
- **Explosives** Void
- **Flammable gases** Void
- **Aerosols**  
Extremely flammable aerosol. Pressurised container: May burst if heated.
- **Oxidising gases** Void
- **Gases under pressure** Void
- **Flammable liquids** Void
- **Flammable solids** Void
- **Self-reactive substances and mixtures** Void
- **Pyrophoric liquids** Void
- **Pyrophoric solids** Void
- **Self-heating substances and mixtures** Void
- **Substances and mixtures, which emit flammable gases in contact with water** Void
- **Oxidising liquids** Void
- **Oxidising solids** Void
- **Organic peroxides** Void
- **Corrosive to metals** Void
- **Desensitised explosives** Void

## SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

## SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

### LD/LC50 values relevant for classification:

#### 246538-78-3 Hydrocarbons, C11-C13, isoalkanes, < 2%aromatics

Oral	LD50	>5,000 mg/kg (rat)
Dermal	LD50	>5,000 mg/kg (rabbit)
Inhalative	LC50/8 h	>5,000 mg/m <sup>3</sup> (rat)

#### 112-34-5 2-(2-butoxyethoxy)ethanol

Oral	LD50	2,410 mg/kg (rat) (OECD Guideline 401)
------	------	--

(Contd. on page 6)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 05.09.2022

Version number 8

Revision: 05.09.2022

**Trade name: CARAMBA Profi High performance rust remover Rasant(Aerosol)**

(Contd. of page 5)

Dermal	LD50	2,764 mg/kg (rabbit) (OECD Guideline 402)
<b>111-76-2 2-butoxyethanol</b>		
Oral	LD50	1,414 mg/kg (gpi)
Inhalative	LC0	>3.1 mg/l (gpi)

- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation**  
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard**  
May be fatal if swallowed and enters airways.

## SECTION 12: Ecological information

### · 12.1 Toxicity

· <b>Aquatic toxicity:</b>	
<b>112-34-5 2-(2-butoxyethoxy)ethanol</b>	
EC50/48 h	>100 mg/l (Daphnia Magna)
<b>111-76-2 2-butoxyethanol</b>	
EC50	1,550 mg/l (daphnia)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.
- **12.7 Other adverse effects**
- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

## SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

## SECTION 14: Transport information

- **14.1 UN number or ID number**
- **ADR, IMDG, IATA** UN1950
- **14.2 UN proper shipping name**
- **ADR, IMDG** AEROSOLS
- **IATA** AEROSOLS, flammable

(Contd. on page 7)

# Safety data sheet

according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 05.09.2022

Version number 8

Revision: 05.09.2022

**Trade name: CARAMBA Profi High performance rust remover Rasant(Aerosol)**

(Contd. of page 6)

· **14.3 Transport hazard class(es)**

· **ADR**



- **Class** 2 5F Gases.  
 · **Label** 2.1

· **IMDG, IATA**



- **Class** 2.1 Gases.  
 · **Label** 2.1  
 · **14.4 Packing group**  
 · **ADR, IMDG, IATA** Void  
 · **14.5 Environmental hazards:**  
 · **Marine pollutant:** No  
 · **14.6 Special precautions for user** Warning: Gases.  
 · **Hazard identification number (Kemler code):** -  
 · **EMS Number:** F-D,S-U  
 · **Stowage Code** SW1 Protected from sources of heat.  
 SW22 For AEROSOLS with a maximum capacity of 1 litre:  
 Category A. For AEROSOLS with a capacity above 1 litre:  
 Category B. For WASTE AEROSOLS: Category C, Clear  
 of living quarters.  
 · **Segregation Code** SG69 For AEROSOLS with a maximum capacity of 1 litre:  
 Segregation as for class 9. Stow "separated from" class 1  
 except for division 1.4.  
 For AEROSOLS with a capacity above 1 litre:  
 Segregation as for the appropriate subdivision of class 2.  
 For WASTE AEROSOLS:  
 Segregation as for the appropriate subdivision of class 2.  
 · **14.7 Maritime transport in bulk according to IMO  
 instruments** Not applicable.  
 · **Transport/Additional information:**
- **ADR**  
 · **Excepted quantities (EQ):** E0  
 · **Limited quantities (LQ)** 1L  
 · **Transport category** 2  
 · **Tunnel restriction code** D  
 · **UN "Model Regulation":** UN 1950 AEROSOLS, 2.1

## SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**  
 Please note TRGS 510.
- **Directive 2012/18/EU**  
 · **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t  
 · **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

GB

(Contd. on page 8)

# Safety data sheet

## according to 1907/2006/EC, Article 31

...das wirkt!

Printing date 05.09.2022

Version number 8

Revision: 05.09.2022

**Trade name: CARAMBA Profi High performance rust remover Rasant(Aerosol)**

(Contd. of page 7)

### SECTION 16: Other information

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.*

· **Relevant phrases**

- H220 Extremely flammable gas.
- H280 Contains gas under pressure; may explode if heated.
- H302 Harmful if swallowed.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- EUH066 Repeated exposure may cause skin dryness or cracking.

· **Abbreviations and acronyms:**

- ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
- IMDG: International Maritime Code for Dangerous Goods
- IATA: International Air Transport Association
- GHS: Globally Harmonised System of Classification and Labelling of Chemicals
- EINECS: European Inventory of Existing Commercial Chemical Substances
- ELINCS: European List of Notified Chemical Substances
- CAS: Chemical Abstracts Service (division of the American Chemical Society)
- LC50: Lethal concentration, 50 percent
- LD50: Lethal dose, 50 percent
- PBT: Persistent, Bioaccumulative and Toxic
- vPvB: very Persistent and very Bioaccumulative
- Flam. Gas 1A: Flammable gases – Category 1A
- Aerosol 1: Aerosols – Category 1
- Press. Gas (Comp.): Gases under pressure – Compressed gas
- Press. Gas (Liq.): Gases under pressure – Liquefied gas
- Acute Tox. 4: Acute toxicity – Category 4
- Skin Irrit. 2: Skin corrosion/irritation – Category 2
- Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
- Asp. Tox. 1: Aspiration hazard – Category 1

· **\* Data compared to the previous version altered.**