

## 1 Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

· **Trade name:** CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

No further relevant information available.

· **Application of the substance / the preparation** Lacquer

### 1.3 Details of the supplier of the safety data sheet

#### · **Manufacturer/Supplier:**

CARAMBA CHEMIE GMBH & Co.KG

WANHEIMERSTR. 334/336

47055 DUISBURG

www.caramba.de

Tel.: +49 (0) 203/77 86 01

#### · **Further information obtainable from:**

Abteilung Labor

Andrea Petersen

andrea.petersen@caramba.de

Tel.: +49 (0)203 / 77 86-189

### 1.4 Emergency telephone number:

Giftnotruf Berlin +49(0)30 30686 790 Beratung in Deutsch und Englisch

## 2 Hazards identification

### 2.1 Classification of the substance or mixture

#### · **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



Xn; Harmful

R20/21: Harmful by inhalation and in contact with skin.



Xi; Irritant

R38: Irritating to skin.



F+; Extremely flammable

R12: Extremely flammable.

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

#### · **Information concerning particular hazards for human and environment:**

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

Warning! Pressurized container.

#### · **Classification system:**

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

### 2.2 Label elements

#### · **Labelling according to EU guidelines:**

The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.

#### · **Code letter and hazard designation of product:**



Xn Harmful

F+ Extremely flammable

#### · **Hazard-determining components of labelling:**

Xylol (Isomeregemisch)

---

**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**


---

(Contd. of page 1)

**· Risk phrases:**

- 12 Extremely flammable.
- 20/21 Harmful by inhalation and in contact with skin.
- 38 Irritating to skin.
- 52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**· Safety phrases:**

- 2 Keep out of the reach of children.
- 16 Keep away from sources of ignition - No smoking.
- 23 Do not breathe spray.
- 24 Avoid contact with skin.
- 29 Do not empty into drains.
- 46 If swallowed, seek medical advice immediately and show this container or label.
- 51 Use only in well-ventilated areas.
- 60 This material and its container must be disposed of as hazardous waste.

**· Special labelling of certain preparations:**

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material.

Buildup of explosive mixtures possible without sufficient ventilation.

**· Classification in accordance with Directive 75/324/EEC: Extremely flammable****· 2.3 Other hazards****· Results of PBT and vPvB assessment**





















- **PBT:** Not applicable.
- **vPvB:** Not applicable.

### 3 Composition/information on ingredients

**· 3.2 Chemical characterization: Mixtures**

· **Description:** Mixture of substances listed below with nonhazardous additions.









**· Dangerous components:**

CAS: 115-10-6 EINECS: 204-065-8	dimethyl ether  F+ R12  Flam. Gas 1, H220; Press. Gas, H280	25-50%
	Xylol (Isomerenmischung)  Xn R20/21;  Xi R38 R10  Flam. Liq. 3, H226;  Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315	10-25%
CAS: 64742-49-0 EC number: 921-024-6	Naphtha, mit Wasserstoff behandelte, leichte (Anmerkung:P)  Xn R65;  Xi R38;  F R11;  N R51/53 R67  Flam. Liq. 2, H225;  Asp. Tox. 1, H304;  Aquatic Chronic 2, H411;  Skin Irrit. 2, H315; STOT SE 3, H336	5-10%
	Ethylacetat CAS-Nr.: 141-78-6  Xi R36;  F R11 R66-67  Flam. Liq. 2, H225;  Eye Irrit. 2, H319; STOT SE 3, H336	5-10%
CAS: 7429-90-5 EINECS: 231-072-3	aluminium powder (stabilised)  F R11-15  Flam. Sol. 1, H228; Water-react. 2, H261	2.5-5%

(Contd. on page 3)

**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**

(Contd. of page 2)

CAS: 7440-66-6 EINECS: 231-175-3	zinc powder -zinc dust (stabilized)  N R50/53  Aquatic Acute 1, H400;  Aquatic Chronic 1, H410	1-2.5%
CAS: 64742-82-1 EINECS: 265-185-4	Naphtha (Erdöl), hydrodesulfunierte schwere  Xn R65;  N R51/53 R10-66  Flam. Liq. 3, H226;  Asp. Tox. 1, H304;  Aquatic Chronic 2, H411	1-2.5%

· **Additional information:** For the wording of the listed risk phrases refer to section 16.

## 4 First aid measures

### · 4.1 Description of first aid measures

#### · **General information:**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

#### · **After inhalation:**

Supply fresh air. If required, provide artificial respiration. Keep patient warm. Consult doctor if symptoms persist.

In case of unconsciousness place patient stably in side position for transportation.

#### · **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

#### · **After eye contact:** Rinse opened eye for several minutes under running water.

#### · **After swallowing:** If symptoms persist consult doctor.

### · 4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

### · 4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

## 5 Firefighting measures

### · 5.1 Extinguishing media

#### · **Suitable extinguishing agents:**

CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

#### · **For safety reasons unsuitable extinguishing agents:** Water with full jet

### · 5.2 Special hazards arising from the substance or mixture

No further relevant information available.

### · 5.3 Advice for firefighters

#### · **Protective equipment:** Mouth respiratory protective device.

## 6 Accidental release measures

### · 6.1 Personal precautions, protective equipment and emergency procedures

Wear protective equipment. Keep unprotected persons away.

### · 6.2 Environmental precautions:

Do not allow product to reach sewage system or any water course.

Inform respective authorities in case of seepage into water course or sewage system.

Do not allow to enter sewers/ surface or ground water.

### · 6.3 Methods and material for containment and cleaning up:

Dispose contaminated material as waste according to item 13.

Ensure adequate ventilation.

### · 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**

(Contd. of page 3)

## 7 Handling and storage

### · 7.1 Precautions for safe handling

Ensure good ventilation/exhaustion at the workplace.

Open and handle receptacle with care.

### · Information about fire - and explosion protection:

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50 °C, i.e. electric lights. Do not pierce or burn, even after use.

Do not spray onto a naked flame or any incandescent material.

### · 7.2 Conditions for safe storage, including any incompatibilities

#### · Storage:

#### · Requirements to be met by storerooms and receptacles:

Store in a cool location.

Observe official regulations on storing packagings with pressurized containers.

#### · Information about storage in one common storage facility: Not required.

#### · Further information about storage conditions:

Store in cool, dry conditions in well sealed receptacles.

Protect from heat and direct sunlight.

#### · 7.3 Specific end use(s) No further relevant information available.

## 8 Exposure controls/personal protection

· **Additional information about design of technical facilities:** No further data; see item 7.

### · 8.1 Control parameters

#### · Ingredients with limit values that require monitoring at the workplace:

##### **115-10-6 dimethyl ether (25-50%)**

WEL Short-term value: 958 mg/m<sup>3</sup>, 500 ppm

Long-term value: 766 mg/m<sup>3</sup>, 400 ppm

##### **Xylol (Isomerengemisch) (10-25%)**

WEL Short-term value: 441 mg/m<sup>3</sup>, 100 ppm

Long-term value: 220 mg/m<sup>3</sup>, 50 ppm

Sk; BMGV

##### **Ethylacetat CAS-Nr.: 141-78-6 (5-10%)**

WEL Short-term value: 400 ppm

Long-term value: 200 ppm

#### · Ingredients with biological limit values:

##### **Xylol (Isomerengemisch) (10-25%)**

BMGV 650 mmol/mol creatinine

Medium: urine

Sampling time: post shift

Parameter: methyl hippuric acid

· **Additional information:** The lists valid during the making were used as basis.

#### · Personal protective equipment:

#### · General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the skin.

Avoid contact with the eyes and skin.

(Contd. on page 5)

---

**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**


---

(Contd. of page 4)

- **Respiratory protection:**  
In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.  
Filter AX
  - **Protection of hands:** Protective gloves
  - **Material of gloves**  
Butyl rubber, BR  
Recommended thickness of the material:  $\geq 0.7$  mm
  - **Penetration time of glove material**  
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.  
Value for the permeation: Level  $\leq 60$  min
  - **Eye protection:** Tightly sealed goggles
- 

## 9 Physical and chemical properties

### · 9.1 Information on basic physical and chemical properties

#### · General Information

##### · Appearance:

Form: Aerosol  
Colour: Silver-coloured

· Odour: Solvent-like  
· Odour threshold: Not determined.

· pH-value: Not determined.

##### · Change in condition

Melting point/Melting range: Undetermined.  
Boiling point/Boiling range: Not applicable, as aerosol.

· Flash point: Not applicable, as aerosol.

· Flammability (solid, gaseous): Not applicable.

· Decomposition temperature: Not determined.

· Self-igniting: Product is not selfigniting.

· Danger of explosion: Product is not explosive. However, formation of explosive air/vapour mixtures are possible.

##### · Explosion limits:

Lower: Not determined.  
Upper: Not determined.

· Vapour pressure: Not determined.

· Density at 20 °C: 0.8 g/cm<sup>3</sup>  
· Relative density: Not determined.  
· Vapour density: Not determined.  
· Evaporation rate: Not applicable.

##### · Solubility in / Miscibility with water:

Not miscible or difficult to mix.

· Partition coefficient (n-octanol/water): Not determined.

##### · Viscosity:

Dynamic: Not determined.  
Kinematic: Not determined.

· 9.2 Other information: No further relevant information available.

**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**

(Contd. of page 5)

## 10 Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

## 11 Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values relevant for classification:**

**Xylol (Isomerengemisch)**

Oral	LD50	8700 mg/kg (rat)
Dermal	LD50	2000 mg/kg (rabbit)
Inhalative	LC50/4 h	6350 mg/l (rat)

**64742-49-0 Naphtha, mit Wasserstoff behandelte, leichte (Anmerkung:P)**

Oral	LD50	> 5840 mg/kg (rat) (OECD Richtlinie 401)
Dermal	LD50	> 2920 mg/kg (rat) (OECD Richtlinie 402) > 2000 mg/kg (rabbit)
Inhalative	LC50/4 h	> 25 mg/l (rat) (OECD Richtlinie 403)

- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**  
The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:  
Harmful  
Irritant

## 12 Ecological information

- **12.1 Toxicity**

· **Aquatic toxicity:**

**Xylol (Isomerengemisch)**

EC50	165 mg/l mg/kg (daphnia)
------	--------------------------

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Harmful to fish
- **Additional ecological information:**
- **General notes:**  
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water  
Do not allow product to reach ground water, water course or sewage system.  
Danger to drinking water if even small quantities leak into the ground.  
Harmful to aquatic organisms

(Contd. on page 7)



**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**



(Contd. of page 6)

- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

## 13 Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

## 14 Transport information

<ul style="list-style-type: none"> <li>· <b>14.1 UN-Number</b></li> <li>· <b>ADR, IMDG, IATA</b></li> </ul>	UN1950
<ul style="list-style-type: none"> <li>· <b>14.2 UN proper shipping name</b></li> <li>· <b>ADR</b></li> <li>· <b>IMDG, IATA</b></li> </ul>	1950 AEROSOLS, ENVIRONMENTALLY HAZARDOUS AEROSOLS
<ul style="list-style-type: none"> <li>· <b>14.3 Transport hazard class(es)</b></li> <li>· <b>ADR</b></li> </ul>	<div style="text-align: center;">  </div>
<ul style="list-style-type: none"> <li>· <b>Class</b></li> <li>· <b>Label</b></li> </ul>	2 5F Gases. 2.1
<ul style="list-style-type: none"> <li>· <b>IMDG, IATA</b></li> </ul>	<div style="text-align: center;">  </div>
<ul style="list-style-type: none"> <li>· <b>Class</b></li> <li>· <b>Label</b></li> </ul>	2 Gases. 2.1
<ul style="list-style-type: none"> <li>· <b>14.4 Packing group</b></li> <li>· <b>ADR, IMDG, IATA</b></li> </ul>	Void
<ul style="list-style-type: none"> <li>· <b>14.5 Environmental hazards:</b></li> <li>· <b>Marine pollutant:</b></li> </ul>	Product contains environmentally hazardous substances: zinc powder -zinc dust (stabilized) No
<ul style="list-style-type: none"> <li>· <b>14.6 Special precautions for user</b></li> <li>· <b>Danger code (Kemler):</b></li> <li>· <b>EMS Number:</b></li> </ul>	Warning: Gases. - F-D,S-U
<ul style="list-style-type: none"> <li>· <b>14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code</b></li> </ul>	Not applicable.
<ul style="list-style-type: none"> <li>· <b>Transport/Additional information:</b></li> </ul>	
<ul style="list-style-type: none"> <li>· <b>ADR</b></li> <li>· <b>Excepted quantities (EQ):</b></li> </ul>	E0

(Contd. on page 8)

**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**

(Contd. of page 7)

· <b>Limited quantities (LQ)</b>	1L
· <b>Transport category</b>	2
· <b>Tunnel restriction code</b>	D

## 15 Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Labelling according to EU guidelines:**  
The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.
- **Code letter and hazard designation of product:**

		Xn Harmful F+ Extremely flammable
---	---	--------------------------------------
- **Hazard-determining components of labelling:**  
Xylol (Isomerengemisch)
- **Risk phrases:**
  - 12 Extremely flammable.
  - 20/21 Harmful by inhalation and in contact with skin.
  - 38 Irritating to skin.
  - 52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- **Safety phrases:**
  - 2 Keep out of the reach of children.
  - 16 Keep away from sources of ignition - No smoking.
  - 23 Do not breathe spray.
  - 24 Avoid contact with skin.
  - 29 Do not empty into drains.
  - 46 If swallowed, seek medical advice immediately and show this container or label.
  - 51 Use only in well-ventilated areas.
  - 60 This material and its container must be disposed of as hazardous waste.
- **Special labelling of certain preparations:**  
Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.  
Do not spray on a naked flame or any incandescent material.  
Buildup of explosive mixtures possible without sufficient ventilation.
- **Classification in accordance with Directive 75/324/EEC:** Extremely flammable
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
  - H220 Extremely flammable gas.
  - H225 Highly flammable liquid and vapour.
  - H226 Flammable liquid and vapour.
  - H228 Flammable solid.
  - H261 In contact with water releases flammable gases.
  - H280 Contains gas under pressure; may explode if heated.
  - H304 May be fatal if swallowed and enters airways.
  - H312 Harmful in contact with skin.
  - H315 Causes skin irritation.

(Contd. on page 9)



**Safety data sheet**  
according to 1907/2006/EC, Article 31



Printing date 28.02.2013

Version number 1

Revision: 30.01.2013

---

**Trade name: CARAMBA Profi High-Performance Zinc Spray Aluminium – light (Aerosol)**

---

(Contd. of page 8)

H319 Causes serious eye irritation.

H332 Harmful if inhaled.

H336 May cause drowsiness or dizziness.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

H411 Toxic to aquatic life with long lasting effects.

R10 Flammable.

R11 Highly flammable.

R12 Extremely flammable.

R15 Contact with water liberates extremely flammable gases.

R20/21 Harmful by inhalation and in contact with skin.

R36 Irritating to eyes.

R38 Irritating to skin.

R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

**\* Data compared to the previous version altered.**

---

GB

---