

1 、 SCOPE

This specification governs the performance of the following Nickel-Metal Hydride cylindrical cell and its stack-up battery.

2 、 DATA OF STACK UP BATTERIES

All data involve voltage and weight of stack-up batteries are equal to the value of unit cell multiplied by the number of unit cell which consisted in the stack-up batteries

Example : Stack-up batteries consisting three unit cells

Nominal voltage of unit cell=1.2V

Nominal voltage of stack-up batteries =1.2V×3=3.6V

3、 RATINGS

Description	Unit	Specification	Condition
Nominal Voltage	V/cell	1.2	Unit cell or stack-up batteries
Minimum Capacity	mAh	2900	Standard Charge/Discharge
Nominal Capacity	mAh	3000	Standard Charge/Discharge
Standard Charge	mA	300 (0.1C)	T ₁ =20±5°C (See Note 1)
	hour	16	
Fast Charge	mA	3000 (1.0C)	- ΔV=0~5mV/cell , Timer Cutoff=120%nominal capacity , Temp.Cutoff=55°C , dT/dt=0.8°C/min, T ₁ =20±5°C
	hour	1.1 approx (See Note 2)	
Trickle Charge	mA	(0.03C)~(0.05C)	T ₁ =20±5°C
Standard discharge	mA	600 (0.2C)	T ₁ = 20±5°C Humidity: Max85%
Discharge Cut-off Voltage	V/cell	1.0	
Storage Temperature	°C	-20~25	Within 1 year*
		-20~35	Within 6 months
		-20~45	Within 1 month
		-20~55	Within 1 week
Typical Weight	Gram	57	unit cell

*To keep the best performance for those not used for a long time,we recommend to charge the cells/batteries at least 30% after discharge entirely in every 6 months.

4、 PERFORMANCE

Unless otherwise stated, tests should be done within one month of delivery under the following conditions:

Ambient Temperature : $20\pm 5^{\circ}\text{C}$

Relative Humidity : $65\pm 20\%$

Notes: Standard Charge/Discharge conditions:

Charge: 300 mA(0.1C)× 16 hours

Discharge: 600 mA(0.2C) to 1.0V/cell

Test	Unit	Specification	Condition	Remarks
Capacity	mAh	≥ 2900	Standard Charge/Discharge	up to 3 cycles are allowed
Open Circuit Voltage(OCV)	V	≥ 1.25	Within 1 hour after standard charge	
Internal Impedance	m Ω	≤ 6	Upon fully charge(1KHz)	
High Rate Discharge(1C)	min	≥ 51	Standard Charge, 1 hour rest before discharge by 1C to 1.0V/cell	up to 3 cycles are allowed
Charge Retention	mAh	≥ 1800 (60%)	Standard Charge, Storage 28days Standard Discharge	$T_1=20\pm 5^{\circ}\text{C}$
IEC Cycle Life	Cycle	≥ 500	IEC61951-2(2003)7.4.1.1	see Note 3
Leakage		No leakage nor deformation	Fully charged at : 300 mA for 48 hrs	
Vibration Resistance		Change of voltage should be less than 0.02V/cell,change of impedance should be less than 5milliohm/cell	Charge the battery at 0.1C for 14hrs,then leave for 24hrs,check battery before/after vibration,amplitude 1.5mm,vibration 3000 CPM,any direction for 60mins.	
Impact Resistance		Change of voltage should be less than 0.02V/cell,change of impedance should be less than 5milliohm/cell	Charge the battery at 0.1C for 14hrs,then leave for 24hrs,check battery before/after dropped,height 50 cm wooden board(thickness 30mm)direction not specified,3 times.	
Maximum continuous discharge current	A	30(10C)		
Maximum momentary discharge current	A	45(15C)		

5、 CONFIGURATION, DIMENSIONS AND MARKINGS

Please refer to the attached drawing.

6、 EXTERNAL APPEARANCE

The cell/battery shall be free from cracks, scars, breakage, rust, discoloration, leakage or deformation.

7、 WARRANTY

One year limited warranty against workmanship and material defects.

8、 CAUTION

[1] Reverse charging is not acceptable.

[2] Charge before use. The cells/batteries are delivered in an uncharged state.

[3] Do not charge/discharge with more than our specified current.

[4] Do not short circuit the cell/battery Permanent damage to the cells/batteries may result.

[5] Do not incinerate or mutilate the cells/batteries.

[6] Do not solder directly to the cells/batteries.

[7] The expected life may be reduced if the cells/batteries are subjected to adverse conditions as:

extreme temperature, deep cycling, excessive overcharge/ over-discharge.

[8] Store the cells/batteries in a cool dry place. Always discharge batteries before packing.

Notes:

[1] T_1 : Ambient Temperature.

[2] Approximate charge time from discharged state, for reference only.


[3] IEC61951-2(2003)7.4.1.1 Cycle Life:

Cycle No.	Charge	Rest	Discharge
1	$0.1C \times 16h$	None	$0.25C \times 2h20min$
2-48	$0.25C \times 3h10min$	None	$0.25C \times 2h20min$
49	$0.25C \times 3h10min$	None	$0.25C$ to $1.0V/cell$
50	$0.1C \times 16h$	1-4h	$0.2C$ to $1.0V/cell$

Cycle 1 to 50 shall be repeated until the discharge duration on any 50th cycle becomes less than 3 h.

MODEL No: ""Uwd/E'3000

Description: 3000 mAh SIZE Ni-MH SC



Specification

Nominal Capacity		3000 mAh	
Nominal Voltage		1.2 V	
Charge current	Standard	300 mA	
	Fast	3000 mA	
Charge time	Standard	16 Hrs	
	Fast	1.1 Hrs	
Ambient Temperature	Charge	Standard	0°C~45°C
		Fast	10°C~45°C
	Discharge		-30°C~60°C
	Storage		-20°C~55°C
Internal Impedance(mΩ) (After Charge)		≤ 6	
Weight		57 g	

