


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		M2	NEW DRAWING PER ECO-11-019045	03APR12	KH	DR



**AMP**  
WIRE RANGE  
26-22 AWG  
STRANDED

- 1 TONGUE MATERIAL THK: 0.46±0.05[.018±.002]
- 2 FOR WIRE INSULATION DIA:1.27[.050] TO 2.08[.082]
- 3 STAMP AMP APPROX AS SHOWN.
- 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD.
- 5 MATERIAL: BODY & SLEEVE: COPPER PER ASTM B152. INSULATION : NYLON
- 6 FINISH: BODY & SLEEVE: TIN PLATE PER ASTM B545. INSULATION: COLOR-YELLOW.

100	LOOSE PC, BOX	8-321035-1
4000	ON TAPE REEL	2-321035-1
1000	LOOSE PC	321035
QTY	PACKAGE TYPE	PART NO

**AMP INCORPORATED**  
**CUSTOMER SERVICE SYSTEMS**

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS  
 PRODUCT INFORMATION CENTER  
 1-800-522-6752

FOR APPLICATION TOOLING INFORMATION  
 TOOLING ASSISTANCE CENTER  
 1-800-722-1111

FOR ORDER ENTRY  
 1-800-526-5142

RECOMMENDED OPERATING TEMPERATURE:  
-

VOLTAGE RATING:  
-

WIRE CROSS SECTIONAL AREA RANGE:  
0.10-0.41mm<sup>2</sup> [202-810] CIR.MIL STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm [INCHES]	
0 PLC	± -
1 PLC	± -
2 PLC	± 0.20[.008]
3 PLC	± -
4 PLC	± -
ANGLES	± 5°

MATERIAL 5 FINISH 6

DWN KIRAN HOLAL 03APR12  
 CHK ROHDE DANIEL 03APR12  
 APVD ROHDE DANIEL 03APR12

**STE** TE Connectivity

NAME WIRE TERMINAL, P.I.D.G.<sup>TM</sup>, 26-22 SPADE #4 STUD

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-321035	-

CUSTOMER DRAWING SCALE 10:1 SHEET 1 OF 1 REV M2